





### **FEATURES**

- \* Ideal for surface mount applications
- \* Easy pick and place
- \* Built-in strain relief
- \* High surge current capability


#### **MECHANICAL DATA**

\* Case: Molded plastic

- \* Epoxy: UL 94V-0 rate flame retardant
- \* Terminals: Solder plated, solderable per MIL-STD-202F, method 208 guranteed
- \* Polarity: Color band denotes cathode end
- \* Mounting position: Any \* Weight: 0.063 gram

# VOLTAGE RANGE 50 to 1000 Volts CURRENT





## MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

TYPE NUMBER	S2A	S2B	S2D	S2G	S2J	S2K	S2M	UNITS
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current		•						
at Ta=75°C	2.0							Α
Peak Forward Surge Current, 8.3 ms single half sine-wave								
superimposed on rated load (JEDEC method)	50						Α	
Maximum Instantaneous Forward Voltage at 2.0A	1.1						V	
Maximum DC Reverse Current Ta=25°C	5.0							μА
at Rated DC Blocking Voltage Ta=100℃	100							μΑ
Typical Junction Capacitance (Note 1)	60							pF
Typical Thermal Resistance R JA (Note 2)	47						°C/W	
Operating and Storage Temperature Range TJ, TsTG	-55—+150							°C

#### NOTES:

- 1. Measured at 1MHz and applied reverse voltage of 4.0V D.C.
- 2. Thermal Resistance from Junction to Ambient.

#### RATING AND CHARACTERISTIC CURVES (S2A THRU S2M)

FIG.1-TYPICAL FORWARD




FIG.2-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.4-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3 - TYPICAL REVERSE

