


■ Three-Terminal Positive Voltage Regulator



■ Simplified outline(SOT-89)

■ Features

- Maximum Output current I_o : 0.1A
- Output Voltage V_o : 5V
- Continuous Total Dissipation P_d : 0.5W ($T_a = 25^\circ\text{C}$)


■ Absolute Maximum Ratings (Operating temperature range applies unless otherwise specified)

| Parameter | Symbol | Rating | Unit |
|--------------------------------------|-----------|------------|------------------|
| Input Voltage | V_i | 30 | V |
| Operating Junction Temperature Range | T_{OPR} | -55 ~ +125 | $^\circ\text{C}$ |
| Storage Temperature Range | T_{STG} | -55 ~ +150 | $^\circ\text{C}$ |

■ Electrical Characteristics ($V_i=10\text{V}$, $I_o=40\text{mA}$, $C_i=0.33\ \mu\text{F}$, $C_o=0.1\ \mu\text{F}$, unless otherwise specified)


| Parameter | Symbol | Test conditions | Min | Typ | Max | Unit |
|--------------------------|--------------|--|------|-----|------|---------------|
| Output Voltage | V_o | $T_J = 25^\circ\text{C}$ | 4.8 | 5.0 | 5.2 | V |
| | | $T_J = 0\sim 125^\circ\text{C}$, $7\text{V} \leq V_i \leq 20\text{V}$, $I_o = 1\text{mA} \sim 40\text{mA}$ | 4.75 | 5.0 | 5.25 | V |
| | | $T_J = 0\sim 125^\circ\text{C}$, $I_o = 1\text{mA} \sim 70\text{mA}$ | 4.75 | 5.0 | 5.25 | V |
| Load Regulation | ΔV_o | $T_J = 25^\circ\text{C}$, $I_o = 1\text{mA} \sim 100\text{mA}$ | | 15 | 60 | mV |
| | | $T_J = 25^\circ\text{C}$, $I_o = 1\text{mA} \sim 40\text{mA}$ | | 8 | 30 | mV |
| Line Regulation | ΔV_o | $7\text{V} \leq V_i \leq 20\text{V}$ | | 32 | 150 | mV |
| | | $T_J = 25^\circ\text{C}$, $8\text{V} \leq V_i \leq 20\text{V}$ | | 26 | 100 | mV |
| Quiescent Current | I_q | $T_J = 25^\circ\text{C}$ | | 3.8 | 6 | mA |
| Quiescent current Change | ΔI_q | $T_J = 0\sim 125^\circ\text{C}$, $8\text{V} \leq V_i \leq 20\text{V}$ | | | 1.5 | mA |
| | | $T_J = 0\sim 125^\circ\text{C}$, $1\text{mA} \leq I_o \leq 40\text{mA}$ | | | 0.1 | mA |
| Output Noise Voltage | V_N | $T_J = 25^\circ\text{C}$, $10\text{Hz} \leq f \leq 100\text{KHz}$ | | 42 | | μV |
| Ripple Rejection | RR | $T_J = 0\sim 125^\circ\text{C}$, $8\text{V} \leq V_i \leq 20\text{V}$, $f = 120\text{Hz}$ | 41 | 49 | | dB |
| Dropout Voltage | V_D | $T_J = 25^\circ\text{C}$ | | 1.7 | | V |

■ Typical Application




Note: Bypass capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators.


■ Typical Characteristics




Output Characteristics




Load Characteristics




Thermal Shutdown



Short Circuit Output Current




Quiescent Current vs Input Voltage



Power Dissipation vs. Ambient Temperature

Package Outline

SOT-89



DIMENSIONS (mm are the original dimensions)

| UNIT | A | b _{p1} | b _{p2} | b _{p3} | c | D | E | e | e ₁ | H _E | L _p | w |
|------|------------|-----------------|-----------------|-----------------|--------------|------------|------------|-----|----------------|----------------|----------------|------|
| mm | 1.6 1.4 | 0.48 0.35 | 0.53 0.40 | 1.8 1.4 | 0.44 0.23 | 4.6 4.4 | 2.6 2.4 | 3.0 | 1.5 | 4.25 3.75 | 1.2 0.8 | 0.13 |

Summary of Packing Options

| Package | Package Description | Packing Quantity | Industry Standard |
|---------|---------------------|------------------|-------------------|
| SOT-89 | Tape/Reel, 7" reel | 1000 | EIA-481-1 |