

Surface Mount Schottky Barrier Rectifier
Reverse Voltage - 20 to 200 V
Forward Current - 2 A
FEATURES

- ◆ Metal silicon junction, majority carrier conduction
- ◆ For surface mounted applications
- ◆ Low power loss, high efficiency
- ◆ High forward surge current capability
- ◆ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ◆ Lead free in comply with EU RoHS 2011/65/EU directives


MECHANICAL DATA

- ◆ Case: SMBF
- ◆ Terminals: Solderable per MIL-STD-750, Method 2026
- ◆ Approx. Weight: 57mg / 0.002oz

Absolute Maximum Ratings and Electrical characteristics

Ratings at 25 ° ambient temperature unless otherwise specified. Single phase, half wave, 60Hz resistive or inductive load, for capacitive load, derate by 20 %







Pinning	
1.Cathode	2.Anode
1	2

Marking Code	
SS22BF	S22B
SS24BF	S24B
SS26BF	S26B
SS28BF	S28B
SS210BF	S210B
SS212BF	S212B
SS215BF	S215B
SS220BF	S220B

Parameter	Symbols	SS22BF	SS24BF	SS26BF	SS28BF	SS210BF	SS212BF	SS215BF	SS220BF	Units					
Maximum Repetitive Peak Reverse Voltage	V_{RRM}	20	40	60	80	100	120	150	200	V					
Maximum RMS voltage	V_{RMS}	14	28	42	56	70	84	105	140	V					
Maximum DC Blocking Voltage	V_{DC}	20	40	60	80	100	120	150	200	V					
Maximum Average Forward Rectified Current	I_{F(AV)}	2.0								A					
Peak Forward Surge Current, 8.3ms Single Half Sine-wave Superimposed On Rated Load (JEDEC method)	I_{FSM}	55				45				A					
Maximum Instantaneous Forward Voltage at 2 A	V_F	0.55		0.70		0.85		0.95		V					
Maximum Instantaneous Reverse Current $T_A = 25^\circ C$ at Rated DC Reverse Voltage $T_A = 100^\circ C$	I_R	0.5 5			0.3 3										
Typical Junction Capacitance ⁽¹⁾	C_j	220			110										
Typical Thermal Resistance ⁽²⁾	R_{θJA}	75								°C/W					
Operating Junction Temperature Range	T_j	-55 ~ +150								°C					
Storage Temperature Range	T_{stg}	-55 ~ +150								°C					

(1) Measured at 1 MHz and applied reverse voltage of 4 V D.C


(2) P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.

Fig.1 Forward Current Derating Curve

Fig.3 Typical Forward Characteristic

Fig.5 Maximum Non-Repetitive Peak Forward Surge Current

Fig.2 Typical Reverse Characteristics

Fig.4 Typical Junction Capacitance

Fig.6- Typical Transient Thermal Impedance


Package Outline


SMBF

Plastic surface mounted package; 2leads



UNIT		A	C	D	E	H _E	e	g	∠
mm	max	1.3	0.26	4.4	3.7	5.5	2.2	1.0	9°
	min	1.1	0.18	4.2	3.5	5.1	1.9		
mil	max	51	10	173	146	216	86	40	9°
	min	43	7	165	138	200	75		

The recommended mounting pad size



Unit: mm(mil)

Summary of Packing Options

Package	Packing Description	Packing Quantity	Industry Standard
SMBF	Tape/Reel,13"reel	5000	EIA-481-1