



X2510 W R S-04 - 9T SN

- ① ②③④⑤ ⑥⑦

- ① Series No.
- ② Category: H-HSG
- ③ Row No.-Pin No. XX-Single row
- ④ Material:N0-PA66 94V-0

Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating:
额定电流:
Withstanding voltage: 1000V AC/minute
耐压电压: 1000V AC/minute
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
接触电阻:≤10mΩ
After environmental testing:≤20mΩ
环境测试后: ≤20mΩ

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.80	10	22.86	26.12
3	5.08	8.34	11	25.40	28.66
4	7.62	10.88	12	27.94	31.20
5	10.16	13.42	13	30.48	33.74
6	12.70	15.96	14	33.02	36.28
7	15.24	18.50	15	35.56	38.82
8	17.78	21.04			
9	20.32	23.58			

X2510H-XX-N0	Nylon 66 UL 94V-0	X2510T	Material
PART NO	Material	Suitable SWB Terminal	Mates With XKB Wafer

REVISIONS					UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE:	
ΔX					ANGULAR	±5°				2510H-XX-N2	
ΔX					L ≤ 4	±0.2	DWN	DATE	VIEW:	PART NO.:	
ΔX					4 < L ≤ 16	±0.3	CHKD	DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD	DATE	SIZE: A4	DWG NO.:	
					L > 63	±0.5	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	
											1.0g
											SHEET
											1/1
											REVISION
											A0