



PCB
PCBLAYOUT

Specifications:

规格:
Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
Current rating: 3A AC / DC
 额定电流: 3A AC / DC
Withstanding voltage: 1000V AC/minute
 耐压电压: 1000V AC/minute
Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
 接触电阻: ≤10mΩ
After environment testing: ≤20mΩ
 环境试验后: ≤20mΩ

X2510 W/V - XX - NO SN

① ②③ ④ ⑤ ⑥

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-180°
- ④ Row No.-Pin No. XX-Single Row
- ⑤ Material: NO-PA66 94V-0
- ⑥ Planting Category SN-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.4
3	5.08	7.62	11	25.4	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	38.10
8	17.78	20.32			
9	20.32	22.86			

X2510WV-XX-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

广东星坤科技股份有限公司

生	日期
發	
Δ	
文件工程章	

REVISIONS

DATE	REVISED	APPROVED

UNSPECIFIED TOLERANCES

www.xkb.cn www.hellixkb.com www.hellixkb.cn

DSND	DATE	SCALE: NA	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X2510WV-XX-N0SN
		WEIGHT	SHEET
		1.0g	1/1
			REVISION
			A0