



**SPECIFICATIONS:**

- 1.ELECTRICAL CHARACTERISTICS:1-1.RATING:DC24V 6A  
1-2.CONTACT RESISTANCE:30m2MAX.(INITIAL)  
1-3.DIELECTRIC WTHSTANDING VOLTAGE:500V AC FOR ONE MINUTE  
1-4.INSULATION RESISTANCE:100MQ MIN. MEASURED BY 500V DC
- 2.MECHANICAL CHARACTERISTICS:  
2-1.Plug it into the mother socket 3 times INSERTION FORCE:0.3~3.0 KGF  
2-2. Plug it into the mother socket 5000 times INSERTION FORCE:0.3~3.0 KG
- 3.SALT FOG:24 Hours
- 4.FOR REFLOW SOLDERING LEAD-FREE PROCESS
5. \* REPRESENT CRITICAL DIMENSIONS.

	MATERIAL	PLATING
TERMINAL 1	Phosphor bronze	NI
Fork hook tube	C3604	NI
plastic	PBT	Black

广东星坤科技股份有限公司

生 日期  
發 日期

文件工程章

REVISIONS

www.xk-ig.cn www.helloxkb.com www.helloxkb.cn

ANGLAR ±5°  
L ≤ 4 ±0.2  
4 < L ≤ 16 ±0.3  
16 < L ≤ 63 ±0.4  
L > 63 ±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: DC PLUG
DWN	DATE	VIEW:	PART NO.: DT-2355525
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
KKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0