



Specifications:

- 规格: XKB
Voltage rating: 600V AC/DC
 额定电压: 600V AC/DC
Current rating: 9A AC/DC
 额定电流: 9A AC/DC
Withstanding voltage: 1500V AC/minute
 耐受电压: 1500V AC/分钟
Temperature range: -25°C~+85°C
 温度范围: -25°C~+85°C
Insulation resistance: ≥1000MΩ
 绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
 接触电阻: ≤10mΩ
After environmental testing: ≤20mΩ
 环境测试后: ≤20兆欧



X9357 W R X-2 XX ES -XX SN XX


- 01 Series No
- 02 Category:W-wafer
- 03 Welding Board Angle:R-Right Angle 180°
- 04 Welding Way: Blank-DIP
- 05 Row No.:Pin No.: 2'XX-2'01P-2'12P
- 06 Plug the Pin&Special NO.:
- ES-With Ears and Screw Holes
- 07 Material:NO-PA66 94V-0/N2-PA66 94V-2
- 08 Plating Category:SN-Bright tin plating
- 09 Color:Blank-Natural Color

000100000

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	—	5.40	2*07	25.20	30.60
2*02	4.20	9.60	2*08	29.40	34.80
2*03	8.40	13.80	2*09	33.60	39.00
2*04	12.60	18.00	2*10	37.80	43.20
2*05	16.80	22.20	2*11	42.00	47.40
2*06	21.00	26.40	2*12	46.20	51.60

000100000

X9357WR-2'XXES-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X9357H
X9357WR-2'XXES-N2SN	Nylon 66 UL 94V-2	Brass	Tin-Plated	X9357H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal



Recommended Pin B Layout
 General Tolerance±0.10

广东星坤科技股份有限公司

生	日期
发	

Δ	文件工程章
MADE IN CHINA	

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
				ANGLAR ±5°
				L ≤ 4 ±0.2
				4 < L ≤ 16 ±0.3
				16 < L ≤ 63 ±0.4
				L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE: X9357WR-2'XXES-N2SN
DWN	DATE	VIEW: ④	PART NO.: 4.20mm Crimp Style Connector
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g SHEET 1/1 REVISION A0