




4.20 [0.165]



4.20 [0.165]



Specifications xxb

规格:

Voltage rating: 600V AC/DC

额定电压: 600V AC/DC

Current rating: 9A AC/DC

额定电流: 9A AC/DC

Withstanding voltage: 1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature

range: -25°C +85°C

温度范围: -25°C +85°C

Insulation resistance: ≥100MΩ

绝缘电阻: ≥100MΩ xxb

Contact resistance: ≤10mΩ

接触电阻: ≤10mΩ

After environmental

testing: ≤20mΩ

环境测试后: ≤20兆欧

X9357WVX-2\*XXX-XX XXXX

- ①
- ②
- ③
- ④
- ⑤
- ⑥
- ⑦
- ⑧
- ⑨

1 Series No.

2 Category: W-AFER

3 Welding Board Angle: V- Stright 180°

4 Weding Way: Blank-DIP

5 Row No Pin No: 2\*XX-2\*01P-2\*12P

6 Plug the Pin & Special No.:

G-Join The glass fiber 15%

7 Material: N0-PAG6 94V-0; N2-PA66 94V-2

9T-PA9T94V-0; 46-PA46 94V-0

8 Plating Category: SN-Bright Tin Plating

9 Color: Blank-Natural Color BK-Black GY-Gray

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*01	5.40	-	2*07	30.60	25.20
2*02	9.60	4.20	2*08	34.80	29.40
2*03	13.80	8.40	2*09	39.00	33.60
2*04	18.00	12.60	2*10	43.20	37.80
2*05	22.20	16.80	2*11	47.40	42.00
2*06	26.40	21.00	2*12	51.60	46.20

X9357WV-2XX-9T5W	Nylon 9T UL 94V-0	Brass	Matte bn	X9357H	
X9357WV-2*XX-N2V01	Nylon 66 UL 94V-2	Brass	Gold-Flash		
X9357WV-2*XX-N2S1	Nylon 66 UL 94V-2	Brass	Tin-Plated		
X9357WV-2*XX-G-N2V01	Nylon 66 UL 94V-2 GF15%	Brass	Gold-Flash		
X9357WV-2*XX-G-N2S1	Nylon 66 UL 94V-2 GF15%	Brass	Tin-Plated		
PART NO	Material	Material(Pin)	Finish(Pin)		Suitable XKB Terminal

广东星坤科技股份有限公司

生	日期
发	
Δ	
文件工程章	

REVISIONS  
www.heloxkb.com

XKB		DSND	DATE	SCALE: NA	MODEL TYPE:
ANGLAR	±5°	DWNN	DATE	VIEW:	X9357WV-2*XXX-XXXX
L ≤ 4	±0.2	CHKD	DATE	UNIT: mm/in	PART NO.:
4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4	4.2 mm Crimp Style Connectors
16 < L ≤ 63	±0.4				DWG NO.:
L > 63	±0.5				
UNSPECIFIED TOLERANCES					

XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT	SHEET	REVISION
			1.0g	1/1	A0