



P.C.B LAYOUT

Specifications :

- Voltage rating: 250VAC / DC
- Current rating: 1A AC / DC
- Withstanding voltage: 300V AC/minute
- Temperature range: -40 to +105
- Insulation resistance: ≥500M Min
- Contact resistance: ≤20M Max
- Material: PA6T 94V-0
- Planting Category: 1U"Gold
- Wave soldering temperature: 255 ± 5°C, 10s

X1321 F R- 2*XX - C43 D24

- ① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: F-Female
- ③ Welding Board Angle: R-Straight 90 °
- ④ Row No -Pin No :2*XX-01P-40P
- ⑤ Plastic height: C=4.3mm
- ⑥ Pin length:D=2.4mm

X1321FR-2*XX-C43D24	PA6T 94V-0	Brass	1U"Gold	X1321W
PART NO	Material	Material(Pin)	Finsh(Pin)	Suitable XKB Terminal

For and on behalf of
XKB INDUSTRIAL PRECISION CO., LIMITED
 香港星坤工業精密有限公司

△ X					ANGULAR	± 5°
△ X					L ≤ 4	± 0.2
△ X					4 < L ≤ 16	± 0.3
△ X					16 < L ≤ 63	± 0.4
MARK	DESCRIPTION	DATE	REVISED	APPROVED	L > 63	± 0.5
REVISIONS					UNSPECIFIED TOLERANCES	

DSND		DATE		SCALE: N/A	MODEL TYPE: X1321FR-2*XX-C43D24	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm	1.27mm Crimp Style Connectors	
APPD		DATE		SIZE: A4	DWG NO.:	
				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0

XKB INDUSTRIAL PRECISION CO., LIMITED