



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤20mΩ
- After environmental testing: ≤30mΩ

X2012 H- XX-N0

① ② ③ ④

- ① Series Number
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-15P
- ④ Material:N0-PA66 UL 94V-0

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.20	5.10	10	18.00	22.20	21.10
03	4.00	8.20	7.10	11	20.00	24.20	23.10
04	6.00	10.20	9.10	12	22.00	26.20	25.10
05	8.00	12.20	11.10	13	24.00	28.20	27.10
06	10.00	14.20	13.10	14	26.00	30.20	29.10
07	12.00	16.20	15.10	15	28.00	32.20	31.10
08	14.00	18.20	17.10	16			
09	16.00	20.20	19.10				

X2012H-XX-N0	PA66 UL 94V-0	X2012T	X2012W
PARY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
MARK	DESCRIPTION

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE: X2012H-XX-N0
				ANGLAR ±5°	DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
				L ≤ 4 ±0.2	CHKD	DATE	UNIT: mm/in	DWG NO.:
				4 < L ≤ 16 ±0.3	APPD	DATE	SIZE: A4	
				16 < L ≤ 63 ±0.4				
				L > 63 ±0.5				
					XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
								SHEET 1/1
								REVISION A0