



Specifications:

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ

After environmental testing:≤30mΩ

环境测试后: ≤30mΩ

X9556 T F-B S N
① ② ③ ④ ⑤ ⑥ ⑦

① Series Number

② Category: T-terminal

③ Shape:F-Female

④ Material:Brass

⑤ Plating style:SN-Bright tin plating

广东星坤科技股份有限公司

生 日期

文件工程章

X9556TF-BSN	Brass	AW#422_28	1.53mm(Max)	Stamping Before Plating 30V Ni/Cu/5n	X9556TM
PART NO	Material	Wire Range	Insulation O.D.	Finish	Suitable XKB

DSND	DATE	SCALE: N/A	MODEL TYPE: X9556TF-PSN
DWN	DATE	VIEW:	PART NO.: 2.54mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	X9556TF-BSN
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

XKB	ANGLAR	±5°
	LS 4	±0.2
	4<LS 16	±0.3
	16<LS 63	±0.4
	LS 63	±0.5
UNSPECIFIED TOLERANCES		

REVISIONS

DATE REVISED APPROVED