



PCB
PCBLAYOUT

Specifications:

规格:
Voltage rating:250V AC/DC
额定电压: 250V AC/DC
Current rating: 3A AC / DC
额定电流: 3A AC / DC
Withstanding voltage: 1000V AC/minute
耐压电压: 1000V AC/minute
Temperature range:-25℃~+85℃
温度范围: -25℃~+85℃
Insulation resistance:≥1000MΩ
绝缘电阻: ≥1000MΩ
Contact resistance: ≤10mΩ
接触电阻:≤10mΩ
After environment testing: ≤20mΩ
环境试验后: ≤20mΩ

X2510 W R - XX A- N0 SN

① ②③ ④⑤ ⑥ ⑦

- ①Series No.
- ②Category: W-WAFER
- ③Welding Board Angle: R-90°
- ④Row No.-Pin No. XX-Single Row
- ⑤Material: N0-PA66 94V-0
- ⑥Planting Category SN-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2	2.54	5.08	10	22.86	25.4
3	5.08	7.62	11	25.4	27.94
4	7.62	10.16	12	27.94	30.48
5	10.16	12.70	13	30.48	33.02
6	12.70	15.24	14	33.02	35.56
7	15.24	17.78	15	35.56	38.10
8	17.78	20.32			
9	20.32	22.86			

X2510WR-XXA-N0SN	Nylon 66 UL 94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Housing

REVISIONS					UNSPECIFIED TOLERANCES		DSND	DATE	SCALE: N/A	MODEL TYPE:	
ΔX					ANGULAR	±5°	DWN	DATE	VIEW:	PART NO.:	
ΔX					L ≤ 4	±0.2	CHKD	DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors	
ΔX					4 < L ≤ 16	±0.3	APPD	DATE	SIZE: A4	DWG NO.:	
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	XKB INDUSTRIAL PRECISION CO., LIMITED			X2510WR-XXA-N0SN	
					L > 63	±0.5	WEIGHT			SHEET	
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn					KKB INDUSTRIAL PRECISION CO., LIMITED			1.0g			REVISION
								1/1			A0