



■ Specifications :

- Voltage rating: 100V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance:  $\geq 500M\Omega$
- Contact resistance:  $\leq 20m\Omega$
- After environmental testing :  $\leq 40m\Omega$

X1515 WVS-XX-LP SW

- ① Series No.
- ② Category : W-WAFER
- ③ Welding Board Angle : V-Straight 180°
- ④ Welding Way:S-SMT
- ⑤ Row No.-Pin No.: XX-02P~15P
- ⑥ Material : LP-LCP 94V-0
- ⑦ Plating Category: SW-Matte Tin Plating

Poles	Dimensions(mm)				Poles	Dimensions(mm)			
	A	B	C	D		A	B	C	D
	7.30	1.50	4.45	6.10		17.80	12.00	14.95	5.00
	8.80	3.00	5.95	7.60		19.30	13.50	16.45	5.00
	10.30	4.50	7.45	9.10		20.80	15.00	17.95	5.00
	11.80	6.00	8.95	10.60		22.30	16.50	19.45	5.00
	13.30	7.50	10.45	12.10		23.80	18.00	20.95	5.00
	14.80	9.00	11.95	13.60		25.30	19.50	22.45	5.00
	16.30	10.50	13.45	5.00		26.80	21.00	23.95	5.00

X1515WVS-XX-LPSW	LCP UL 94V-0	Phosphor Bronze	Brass	Matte Tin-Plated	X1515H
PART NO	Material	Material(pin)	Material	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X1515WVS-XX-LPSW
DWN	DATE	VIEW:	PART NO.: 1.5mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn