



X9357 W R X- XX X- XX SN XX
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧

- 01 Series No.
- 02 Category:W-wafer
- 03 Welding Board Angle: R-Right Angle 90°
- 04 Welding Way: Blank-DIP;
- 05 Row No.-Pin No.:XX-02P-06P
- 06 Special NO.:
- 07 Material:N0-PA6694V-0;LP-LCP 94V-0
 N2-PA66 94V-2;9T-PA9T94-0
 6T-PA6T 94V-0
- 08 Planting Category: SN-Bright tin plating
- 09 Color:Blank-natural color ;

Specifications:
 规格:
 Voltage rating:600V AC/DC
 额定电压: 600V AC/DC
 Current rating:9A AC/DC
 额定电流: 9A AC/DC
 Withstanding voltage:1500V
 AC/minute
 耐受电压: 1500V AC/分钟
 Temperature
 range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance:≤10mΩ
 接触电阻: ≤10mΩ
 After environmental
 testing:≤20mΩ
 环境测试后: ≤20兆欧

Poles	Dimensions(mm)	
	A	B
02	4.20	9.60
03	8.40	13.80
04	12.60	18.00
05	16.80	22.20
06	21.00	26.40

X9357WR-XX-9TSN	Nylon 9T UL 94V-0	Brass	Tin-Plated	X9357H
X9357WR-XX-6TSN	Nylon 6T UL 94V-0			
X9357WR-XX-LPSN	LCP UL 94V-0			
X9357WR-XX-N0SN	Nylon 66 UL 94V-0			
X9357WR-XX-N2SN	Nylon 66 UL 94V-2			
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X9357WR-XX-XXSN
DWNN	DATE	VIEW:	PART NO.: 2.54 mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0