


■ Specifications :

- Voltage rating: 250V A C / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X3025 WR X-2'XX X-N0 XX XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲

- ① Series No.
- ② Category : Wafer
- ③ Welding Board Angle: R-90°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: 2'XX-2'01P~2'12P
- ⑥ Special NO.:
- ⑦ Material: 46-P A46 94V-0
- ⑧ Plating Category: G01-Contact Gold Flash, SN-Bright tin plating
- ⑨ Color: Blank-natural color



Poles	Dimensions (mm)	
	A	B
2'01	---	6.65
2'02	3.00	9.65
2'03	6.00	12.65
2'04	9.00	15.65
2'05	12.00	18.65
2'06	15.00	21.65
2'07	18.00	24.65
2'08	21.00	27.65
2'09	24.00	30.65
2'10	27.00	33.65
2'11	30.00	36.65
2'12	33.00	39.65

Scale 1:3

X3025WR-2'XX-46G01	PA46 UL 94V-0	Brass	Contact Gold	X3025H
X3025WR-2'XX-46SN	PA46 UL 94V-0	Tin-Plated	Tin-Plated	
Part No.	Material	Material(Pin)	Finish(Pin)	Mates With XKB Housing

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
			XKB	ANGLAR ±5°
				L ≤ 4 ±0.2
				4 < L ≤ 16 ±0.3
				16 < L ≤ 63 ±0.4
				L > 63 ±0.5

DSND	DATE	SCALE: NA	MODEL TYPE:
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0