



**Specifications:**

规格:  
 Voltage rating:250V AC/DC  
 额定电压: 250V AC/DC  
 Current rating:3A AC/DC  
 额定电流: 3A AC/DC  
 Withstanding voltage:800V AC/minute  
 耐受电压: 800V AC/分钟  
 Temperature range:-25°C~+85°C  
 温度范围: -25°C~+85°C  
 Insulation resistance:≥1000MΩ  
 绝缘电阻: ≥1000MΩ  
 Contact resistance:≤10mΩ  
 接触电阻: ≤10mΩ  
 After environmental testing:≤20mΩ  
 环境测试后: ≤20兆欧

X2026 W R-2xXX A- XX SN

① ② ③ ④ ⑤ ⑥ ⑦

- 1.Series No
- 2.Category:W-WAFER
- 3.Welding Board Angle:R-Right Angle 90°
- 4.Row No-Pin No:2xXX-2x02P~2x22P
- 5.Plug the Pin&Special NO:  
A-With Lock on both side
- 6.Material:9T-PA9T 94V-0;N0-PA66 94V-0
- 7.Plating Category:SN-Bright Tin Plating

poles	Dimensions(mm)			poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C		A	B	C
2x02	2.00	8.00	4.60	2x09	16.00	22.00	18.60	2x16	30.00	36.00	32.60
2x03	4.00	10.00	6.60	2x10	18.00	24.00	20.60	2x17	32.00	38.00	34.60
2x04	6.00	12.00	8.60	2x11	20.00	26.00	22.60	2x18	34.00	40.00	36.60
2x05	8.00	14.00	10.60	2x12	22.00	28.00	24.60	2x19	36.00	42.00	38.60
2x06	10.00	16.00	12.60	2x13	24.00	30.00	26.60	2x20	38.00	44.00	40.60
2x07	12.00	18.00	14.60	2x14	26.00	32.00	28.60				
2x08	14.00	20.00	16.60	2x15	28.00	34.00	30.60				

X2026WR-2xXXA-9T SN	PA9T UL 94V-0	Brass	Tin-Plated	X2026H-A
X2026WR-2xXXA-N0 SN	PA66 UL 94V-0			X2026H-A
PART NO	Material	Material(pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司  
 Recommended P.C.B Layout

General Tolerance±0.05

生	日期	DESCRIPTION	DATE	REVISED	APPROVED	units:	mm
ΔX						tolerance:	
ΔX						X.X	±0.2mm
ΔX						X.XX	±0.1mm
MARK						X.XXX	±0.05mm
UNSPECIFIED TOLERANCES							

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector	
DWN		DATE		VIEW:	PART NO.: 2.00mm Crimp Style Connectors	
CHKD		DATE		UNIT: mm/in	DWG NO.: X2026WR-2xXXA-XXSN	
APPD		DATE		SIZE: A4		
KKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0

文件工程章