



### Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10m Ω
- After environmental testing : ≤20m Ω
- Mark"\*\*\*"Indicate Dimensions Need To Controlled In Emphasis



X3025 WVS-XX D-LP XX XX

① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫

- ① Series No.
- ② Category :
- ③ W-wafer
- ④ Welding Board Angle: V-180°
- ⑤ Welding Way: S-SMT
- ⑥ Row No.-Pin No. XX-Single row
- ⑦ Special NO.
- ⑧ D-Solder Tabs
- ⑨ Material: LP-LCP 94V-0
- ⑩ Plating Category: V\*\*\*All Gold-Plated G\*\*Gold-Plated Contact '01-Gold Flash ; '02-2U'; '03-3U'; '05-5U' '10-10U' ;'15-15U'; '30-30U'; '50-50U' SN-Bright tin plating 70U" SN1-Bright tin plating 120U"/Min. ; SW-Fog Tin plating
- ⑪ Color: Blank-natural color

Poles	Dimension 5(mm)		
	A	B	C
02	9.70	3.00	12.50
03	12.70	6.00	15.50
04	15.70	9.00	18.50
05	18.70	12.00	21.50
06	21.70	15.00	24.50
07	24.70	18.00	27.50
08	27.70	21.00	30.50
09	30.70	24.00	33.50
10	33.70	27.00	36.50
11	36.70	30.00	39.50
12	39.70	33.00	42.50

X3025 WVS-XXD-LPSW	LCP UL 94V-0	Brass	Tin Plated Fog	Brass	Tin Plated Fog	X3025H	
X3025 WVS-XXD-LPSN	LCP UL 94V-0		Tin-Plated		Tin-Plated		
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)		Mates With XKB 5.70Housing

广东星坤科技股份有限公司  
P.C.B. LA YOUT  
日期  
文件工程章

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: NA	MODEL TYPE: X3025WVS-XXD-LPXX
DWNN	DATE	VIEW: <input checked="" type="checkbox"/> A	PART NO.:
CHKD	DATE	UNIT: mm/in	3.00mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0