



Recommended PCB Layout
General Tolerance ±0.05



Specifications:

- Voltage rating: 250V AC/DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

C3030 WRS-2*XX D-LP XX XX
① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: R-Straight 180°
- ④ Welding Way: S-SMT
- ⑤ Row No.-Pin No.: 2*XX-2x02P~2x22P
- ⑥ Plug the Pin & Special No.: D-With Solder Tabs
- ⑦ Material: LP-LCP 94V-0
- ⑧ Plating Category: SN-Bright Tin Plating; G05-Contact Gold 5u" SW-Fog Tin plating
- ⑨ Color: Blank-Natural Color

Poles	Dimensions (mm)			Poles	Dimensions (mm)	
	AB				AB	
2*01	6.65	---		2*07	24.65	18.00
2*02	9.65	3.00		2*08	27.65	21.00
2*03	12.65	6.00		2*09	30.65	24.00
2*04	15.65	9.00		2*10	33.65	27.00
2*05	18.65	12.00		2*11	36.65	30.00
2*06	21.65	15.00		2*12	39.65	33.00

C3030WRS-2*XXD-LPSW	LCP UL 94V-0	Brass	Matte tin	Brass	Tin-Plated	X3030H
C3030WRS-2*XXD-LPG05			Ni:50u"Min;Sn:120u"Min; Contact Area Gold:5u" Min.			
C3030WRS-2*XXD-LPSN			Tin-Plated			
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	

广东星坤科技股份有限公司

生效日期	文件工程章	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: Wire to board connector
DWN		DATE		VIEW:	PART NO.: 3.00 mm Crimp Style Connectors
CHKD		DATE		UNIT: mm/in	DWG NO.: C3030WRS-2*XXD-XXXX
APPD		DATE		SIZE: A4	WEIGHT · SHEET · REVISION 1.0g · 1/1 · A0
KKB INDUSTRIAL PRECISION CO., LIMITED					