


P.C.B LAND DIMENSION

**SPECIFICATION**

Contact Rating: 50mA, 12V DC  
 Contact Resistance: 100mΩ max  
 Insulation Resistance: 100mΩ min. 500V DC  
 Dielectric Strength: 250V AC/1minute



CIRCUIT DIAGRAM

**REFERENCE DRAWING**

8.40 mm	6.80 mm	BLACK	BLACK	160±30gf	100,000 Cycles
"H"	"L"	STEM COLOR	CASE COLOR	O/FORCE	LIFE

					units: mm	DSND		DATE		SCALE: N/A	MODEL TYPE: <b>TACT SWITCH</b>				
					tolerance:	DWN		DATE		VIEW:	PART NO.:				
Δx					X.X ±0.2mm	CHKD		DATE		UNIT: mm	DWG NO.: <b>TC-TL54-C</b>				
Δx					X.XX ±0.1mm	APPD		DATE		SIZE: A4					
MARK	DESCRIPTION	DATE	REVISED	APPROVED	X.XXX ±0.05mm	UNSPECIFIED TOLERANCES					WEIGHT	SHEET	REVISION		
REVISIONS										<b>XKB INDUSTRIAL PRECISION CO., LIMITED</b>			1.0g	1/1	A0
www.xk-dg.cn www.helloxkb.com www.helloxkb.cn															