



■ Specifications :

- Voltage rating: 250V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 800V AC/minute
- Temperature range: -25°C~+85°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤20mΩ
- After environmental testing : ≤20mΩ

X2000 W R-XX A- PT SN

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Stright 90°
- ④ Row No.-Pin No.: XX-02P~16P
- ⑤ Plug the Pin & Special NO.:A-With Kink
- ⑥ Material : PT-PBT 94V-0
- ⑦ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.00	6.00	09	18.00	22.00
03	4.00	8.00	10	20.00	24.00
04	6.00	10.00	11	22.00	26.00
05	8.00	12.00			
06	10.00	14.00			
07	12.00	16.00			
08	14.00	18.00			
09	16.00	20.00			

X2000WR-XXA-PTSN	PBT UL 94V-0	Brass	Tin-Plated	X2000H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2000WR-XXA-PTSN
DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn