



SPECIFICATION
 Contact Rating: 50mA, 12V DC
 Contact Resistance: 100mΩ max
 Insulation Resistance: 100mΩ min. 500V DC
 Dielectric Strength: 250V AC/1minute
 Travel: 1.2mm
 Operating Temp: -30 ~ +85
 Storage Temp: -30 ~ +80

PAPT NO	TC-1117D-X
Operating Force	A:120gf B:160gf C:260gf
Height	H:5.0

ITEM	PAPT NAMF	TER.NO	QTY	MATERIAL	FINISHING	REMARK
①	Terminal	2	Brass (0.30t)	Plating silvering		
②	Base	1	Pa46			
③	Keystake	1	Silica gel			

广东星坤科技股份有限公司

生效	日期
ΔX	
ΔX	
ΔX	

文件工程章

REVISIONS	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND		DATE		SCALE: N/A	MODEL TYPE: TACT SWITCH	
DWN		DATE		VIEW:	PART NO.:	
CHKD		DATE		UNIT: mm/in	DWG NO.:	
APPD		DATE		SIZE: A4	TC-1117D-X	
XKB INDUSTRIAL PRECISION CO., LIMITED				WEIGHT	SHEET	REVISION
				1.0g	1/1	A0