



Specifications:
 规格:
 Voltage rating:250V AC/DC
 额定电压: 250V AC/DC
 Current rating: 3A AC / DC
 额定电流: 3A AC / DC
 Withstanding voltage: 1000V AC/minute
 耐压电压: 1000V AC/minute
 Temperature range:-25℃~+85℃
 温度范围: -25℃~+85℃
 Insulation resistance:≥1000MΩ
 绝缘电阻: ≥1000MΩ
 Contact resistance: ≤10mΩ
 接触电阻: ≤10mΩ
 After environmental testing:≤20mΩ
 环境测试后: ≤20mΩ

X2508 W V S- XX X - 9T XX XX

- ① Series No.
- ② Category: W-WAFER
- ③ Welding Board Angle: V-Stringht 180°
- ④ Welding Way:
- ⑤ Row No.-Pin No. XX-02P~15P
- ⑥ Plug the Pin & Special No.
- ⑦ Material: 9T-PA9T 94V-0
- ⑧ Plating Category SW-Fog Tin plating
- ⑨ Color: Blank-Natural Color

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
2	2.50	10.00	5.30	10	22.50	30.00	6.40
3	5.00	12.50		11	25.00	32.50	
4	7.50	15.00		12	27.50	35.00	
5	10.00	17.50	6.40	13	30.00	37.50	
6	12.50	20.00		14	32.50	40.00	
7	15.00	22.50		15	35.00	42.50	
8	17.50	25.00					
9	20.00	27.50					

X2508WVS-XX-9TSW	PA9T UL 94V-0	Brass	Tin-Plated	Brass	Tin Plating	X2508H
PART NO	Material	Material(Pin)	Finish(Pin)	Material (Solder Tabs)	Finish (Solder Tabs)	Mates With Housing

广东星坤科技股份有限公司
 RECOMMENDED PCB LAYOUT

生	日期
發	
Δ	
文件工程章	

REVISIONS	DATE	REVISED	APPROVED
UNSPECIFIED TOLERANCES			

DSND	DATE	SCALE: NA	MODEL TYPE:
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	2.50 mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			X2508WVS-XX-9TSW
		WEIGHT	SHEET
		1.0g	1/1
		REVISION	A0