


P/N	R/C
U261-24XXN-4B0416	C2, C3(0.1uF X5R 6.3V) IC, HUSB330DN6(DFN-6L)







U261-24XXN-4B0416

C TYPE PLUG:

PCB:



- 1: Au
- 2: Ni
- 1:Au1u"
- 2:Au3u"
- 4:Au15u"
- 5:Au30u"



REMARKS:

- 1.CONTACT INSERTION AND WITHDRAW FORCE :
  - 1.Insertion force : 5N-20N max.
  2. Withdrawal force : 8N-20N.
  - 3.Durability : 10000Cycles.
- 2.ELECTRIC PROPERTY :
  - 1.Contact current rating : 3A.
  - 2.Dielectric Strength : 100V AC(RMS).
  - 3.Insulation Resistance : 100 megaohms min.
  4. Contact resistance : 40m0hms MAX.FOR VBUS,GND AND OTHER CONTACT 50m0hms MAX.AFTER ENVIRONMENT TEST
- 3.AMBIENT TEMPERATURE :
  - 1.Operating temperature : -55°C to +85°C.

A12	A11	A10	A9	A8	A7	A6	A5	A4	A3	A2	A1
GND	RX2+	RX2-	Vbus	SBU1	D-	D+	CC	Vbus	TX1-	TX1+	GND
GND	TX2+	TX2-	Vbus	Vconn			SBU2	Vbus	RX1-	RX1+	GND
B1	B2	B3	B4	B5	B6	B7	B8	B9	B10	B11	B12

ITEM	DESCRIPTION	MATERIAL	REMARKS
6	Shrapnel	SUS T=0.10mm	
5	Shell	SUS T=0.15mm	Ovep-plating: Ni
4	Terminal	C7025 T=0.15mm	Ovep-plating:Au Ni/Sn
3	Latch	SUS T=0.4mm	
2	Housing	LCP	UL94-0
1	Housing Stopper	LCP	UL94-0

MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES
Δx					ANGLAR ±5°
Δx					L ≤ 4 ±0.2
Δx					4 < L ≤ 16 ±0.3
Δx					16 < L ≤ 63 ±0.4
Δx					L > 63 ±0.5

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	3.1 TYPE C
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:
			U261-24XXN-4B0416
			WEIGHT
			1.0g
			SHEET
			1/1
			REVISION
			A0