



SPECIFICATION:

1. Material

Housing Material:High temperature thermoplastic
 Contact Terminal:High Grade Copper Alloy
 Merallic Shell:Stainless Steel
 Inner Ground Cover Shell:Stainless Steel
 Mid Plate:Stainless Steel

2. Mechanical:

2.1.Mating force:5-20Nf;
 2.2.Unmating force:Initial:8-20Nf;Final:6-20Nf;
 2.3.Durability:5000 Cycles;

3.Electrical:

3.1.Current Rating:3A
 3.2.Voltage Rating:20V Max.;;
 3.3.Dielectric Withstanding

volage:100Vac,60S,10mA;

3.4.Contact resistance:40m Ohms Max.;;
 3.5.Insulation Resistance:100M Ohms Min.;;

4.Environmental:

4.1.Operating temperature:-40°C~+85°C;
 4.2.Salt Spray Test:24H Min.(No oxidation or rust);

U262-16XN-4BC21665

1:Au1u"
 2:Au3u"
 4:Au15u"
 5:Au30u"
 1:PBT
 2:PA6T
 3:PA9T
 4:LCP

1:WITH
 2:WITHOUT
 W:WHITE
 B:BLACK

					ANGLAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE:	3.1 TYPE C		
					L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:			
					4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm/in	DWG NO.:	U262-16XN-4BC21665		
					16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	WEIGHT	1.0g		
					L > 63	±0.5	XKB INDUSTRIAL PRECISION CO.,LIMITED					SHEET	1/1	
REVISIONS					UNSPECIFIED TOLERANCES								REVISION	A0
MARK	DESCRIPTION	DATE	REVISED	APPROVED	www.xk-dg.cn www.helloxkb.com www.helloxkb.cn									