



02P~03P Shape Scale1:1



02P~03P Shape
Scale 1:2



04~05P Shape
Scale 1:2

■ Specifications :

- Voltage rating: 100V AC / DC
- Current rating: 2A AC / DC
- Withstanding voltage: 500V AC/minute
- Temperature range: -40°C~+85°C
- Insulation resistance: ≥500MΩ
- Contact resistance: ≤20mΩ
- After environmental testing:≤40mΩ

X1515 H- XX-N0 HF

① ② ③ ④ ⑤

- ① SeriesNumber
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-15P
- ④ Material:N0-PA66;PT-PBT 94V-0
- ⑤ HF-Halogen Free

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	1.50	7.30	4.25	09	12.00	17.80	14.75
03	3.00	8.80	5.75	10	14.0	17.30	16.25
04	4.50	10.30	7.25	11	15.0	18.30	17.75
05	6.00	11.80	8.75	12	17.0	20.30	19.25
06	7.50	13.30	10.25	13	19.0	22.30	20.75
07	9.00	14.80	11.75	14	24.0	27.30	22.25
08	10.50	16.30	13.25	15	24.0	27.30	23.75

X1515H-XX-N0	PA66 UL 94V-0	X1515T	X1515W
X1515H-XX-N0HF	PA66 UL 94V-0 (Halogen Free)		
X1515H-XX-PT	PBT UL 94V-0		
PARY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

广东星坤科技股份有限公司

生效

ΔX	日期
ΔX	日期
ΔX	日期
MARK	DESCRIPTION

REVISIONS

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X1515H-XX-N0HF
CHKD	DATE	UNIT: mm/in	PART NO.: 1.5mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章