H-Bridge in APM16 Series for LLC and Phase-shifted DC-DC Converter

NXV65HR82DS1, NXV65HR82DS2, NXV65HR82DZ1, NXV65HR82DZ2

Features

- SIP or DIP H-Bridge Power Module for On-board Charger (OBC) in EV or PHEV
- 5 kV/1 s Electrically Isolated Substrate for Easy Assembly
- Creepage and Clearance per IEC60664-1, IEC 60950-1
- Compact Design for Low Total Module Resistance
- Module Serialization for Full Traceability
- Lead Free, RoHS and UL94V-0 Compliant
- Automotive Qualified per AEC Q101 and AQG324 Guidelines

Applications

• DC-DC Converter for On-board Charger in EV or PHEV


Benefits

- Enable Design of Small, Efficient and Reliable System for Reduced Vehicle Fuel Consumption and CO₂ Emission
- Simplified Assembly, Optimized Layout, High Level of Integration, and Improved Thermal Performance




ON Semiconductor®

www.onsemi.com



APMCA-A16 16 LEAD CASE MODGF



APMCA-B16 16 LEAD CASE MODGJ

MARKING DIAGRAM

XXXXXXXXXX ZZZ ATYWW NNNNNNN

XXXX = Specific Device Code

ZZZ = Lot ID

AT = Assembly & Test Location

Y = Year W = Work Week NNN = Serial Number

ORDERING INFORMATION

See detailed ordering, marking and shipping information on page 10 of this data sheet.

Pin Configuration and Block Diagram




Figure 1. Pin Configuration

Table 1. PIN DESCRIPTION

Pin Number	Pin Name	Pin Description
1, 2	AC1	Phase 1 Leg of the H–Bridge
3	Q1 Sense	Source Sense of Q1
4	Q1 Gate	Gate Terminal of Q1
5, 6	B+	Positive Battery Terminal
7, 8	B-	Negative Battery Terminal
9	Q2 Sense	Source Sense of Q2
10	Q2 Gate	Gate Terminal of Q2
11	Q4 Sense	Source Sense of Q4
12	Q4 Gate	Gate Terminal of Q4
13	Q3 Sense	Source Sense of Q3
14	Q3 Gate	Gate Terminal of Q3
15, 16	AC2	Phase 2 Leg of the H–Bridge

Block Diagram




Figure 2. Schematic

Table 2. ABSOLUTE MAXIMUM RATINGS (T_J = 25°C, Unless Otherwise Specified)

Symbol	Parameter	Max	Unit
V _{DS} (Q1~Q4)	Drain-to-Source Voltage	650	V
V _{GS} (Q1~Q4)	Gate-to-Source Voltage	±20	V
I _D (Q1~Q4)	Drain Current Continuous (T _C = 25°C, V _{GS} = 10 V) (Note 1)	26	Α
	Drain Current Continuous (T _C = 100°C, V _{GS} = 10 V) (Note 1)	17	Α
P _D	Power Dissipation (Note 1)	126	W
TJ	Maximum Junction Temperature	-55 to +150	°C
T _C	Maximum Case Temperature	-40 to +125	°C
T _{STG}	Storage Temperature	-40 to +125	°C

Stresses exceeding those listed in the Maximum Ratings table may damage the device. If any of these limits are exceeded, device functionality should not be assumed, damage may occur and reliability may be affected.

Table 3. SINGLE PULSE AVALANCHE ENERGY

Symbol	Parameter	Max	Unit
E _{AS} (Q1~Q4)	Single Pulsed Avalanche Energy (Note 2)	510	mJ
E _{AS} (Q1~Q4)	Single Pulsed Avalanche Energy (Note 2)	21	mJ
I _{AS}	Avalanche Current	4.8	Α

^{2. 510} mJ is characterized at T_J = 25°C, L = 44.3 mH, I_{AS} = 4.8 A, V_{DD} = 145 V. 21 mJ is 100% tested at T_J = 25°C, L = 1 mH, I_{AS} = 4.8 A, V_{DD} = 145 V.

Table 4. COMPONENTS (Note 3)

Device	Parameter	Condition	Min	Тур	Max	Unit
Capacitor (Snubber) AEC Q200 qualified	Capacitance	$T_J = 25^{\circ}C$	135	150	165	nF
AEC Q200 qualified	Rated Voltage		_	630	-	V

^{3.} These values are obtained from the specification provided by the manufacturer.

DBC Substrate

 0.63 mm Al_2O_3 alumina with 0.3 mm copper on both sides. DBC substrate is NOT nickel plated.

Lead Frame

OFC copper alloy, 0.50 mm thick. Plated with 8 um to 25.4 um thick Matte Tin

Flammability Information

All materials present in the power module meet UL flammability rating class 94V-0.

Compliance to RoHS Directives

The power module is 100% lead free and RoHS compliant 2000/53/C directive.

Solder

Solder used is a lead free SnAgCu alloy.

Solder presents high risk to melt at temperature beyond 210°C. Base of the leads, at the interface with the package body, should not be exposed to more than 200°C during mounting on the PCB or during welding to prevent the re-melting of the solder joints.

^{1.} Maximum continuous current and power, without switching losses, to reach $T_J = 150^{\circ}\text{C}$ respectively at $T_C = 25^{\circ}\text{C}$ and $T_C = 100^{\circ}\text{C}$; defined by design based on MOSFET $R_{DS(ON)}$ and $R_{\theta JC}$ and not subject to production test

Table 5. ELECTRICAL SPECIFICATIONS (T_J = 25°C, Unless Otherwise Specified)

Symbol	Parameter	Conditions	Min	Тур	Max	Unit
BV _{DSS}	Drain-to-Source Breakdown Voltage	I _D = 1 mA, V _{GS} = 0 V	650	-	_	V
V _{GS(th)}	Gate to Source Threshold Voltage	$V_{GS} = V_{DS}$, $I_D = 0.97$ mA	3.0	-	5.0	V
R _{DS(ON)}	Q1 – Q4 MOSFET On Resistance	V _{GS} = 10 V, I _D = 20 A	-	73	82	mΩ
R _{DS(ON)}	Q1 – Q4 MOSFET On Resistance	V _{GS} = 10 V, I _D = 20 A, T _J = 125°C (Note 4)	-	133	-	mΩ
9 _{FS}	Forward Transconductance	V _{DS} = 20 V, I _D = 20 A (Note 4)	-	29	-	S
I _{GSS}	Gate-to-Source Leakage Current	V _{GS} = ±30 V, V _{DS} = 0 V	-100	-	+100	nA
I _{DSS}	Drain-to-Source Leakage Current	V _{DS} = 650 V, V _{GS} = 0 V	-	-	10	μΑ
DYNAMIC CHARACTERISTICS (Note 4)						
_		1/4 400.1/		0000		

C _{iss}	Input Capacitance	V _{DS} = 400 V	_	3608	-	pF
C _{oss}	Output Capacitance	V _{GS} = 0 V f = 1 MHz	_	72.3	-	pF
C _{rss}	Reverse Transfer Capacitance	1 - 1 141112	_	5.56	-	pF
C _{oss(eff)}	Effective Output Capacitance	V _{DS} = 0 to 520 V V _{GS} = 0 V	-	448	ı	pF
Rg	Gate Resistance	f = 1 MHz	_	1.7	-	Ω
Q _{g(tot)}	Total Gate Charge	V _{DS} = 380 V	_	79.7	-	nC
Q _{gs}	Gate-to-Source Gate Charge	I _D = 20 A V _{GS} = 0 to 10 V	_	24.9	-	nC
Q_{gd}	Gate-to-Drain "Miller" Charge	VGS = 0 10 V	_	31.9	_	nC

SWITCHING CHARACTERISTICS (Note 4)

t _{on}	Turn-on Time	V _{DS} = 400 V	-	96	-	ns
t _{d(on)}	Turn-on Delay Time	I _D = 20 A V _{GS} = 10 V	_	54	-	ns
t _r	Turn-on Rise Time	$R_G = 4.7 \Omega$	_	42	_	ns
t _{off}	Turn-off Time		_	117	_	ns
t _{d(off)}	Turn-off Delay Time		_	84	_	ns
t _f	Turn-off Fall Time		_	33	_	ns

BODY DIODE CHARACTERISTICS

V_{SD}	Source-to-Drain Diode Voltage	I _{SD} = 20 A, V _{GS} = 0 V	-	1.1	1	V
T _{rr}	Reverse Recovery Time	$V_{DS} = 520 \text{ V, } I_{D} = 20 \text{ A,}$	-	107	-	ns
Q_{rr}	Reverse Recovery Charge	$d_l/d_t = 100 \text{ A/}\mu\text{s} \text{ (Note 4)}$	-	430	-	nC

Product parametric performance is indicated in the Electrical Characteristics for the listed test conditions, unless otherwise noted. Product performance may not be indicated by the Electrical Characteristics if operated under different conditions.

Table 6. THERMAL RESISTANCE

Parameters		Min	Тур	Max	Unit
R _{θJC} (per chip)	Q1~Q4 Thermal Resistance Junction-to-Case (Note 5)	-	0.7	0.99	°C/W
R _{θJS} (per chip)	Q1~Q4 Thermal Resistance Junction-to-Sink (Note 6)	-	1.32	_	°C/W

Test method compliant with MIL STD 883-1012.1, from case temperature under the chip to case temperature measured below the package at the chip center, Cosmetic oxidation and discoloration on the DBC surface allowed

 Table 7. ISOLATION (Isolation resistance at tested voltage from the base plate to control pins or power terminals.)

Test	Test Conditions	Isolation Resistance	Unit
Leakage @ Isolation Voltage (Hi-Pot)	V _{AC} = 5 kV, 50 Hz	100M <	Ω

^{4.} Defined by design, not subject to production test

^{6.} Defined by thermal simulation assuming the module is mounted on a 5 mm Al-360 die casting material with 30 um of 1.8 W/mK thermal interface material

PARAMETER DEFINITIONS

Reference to Table 5: Parameter of Electrical Specifications

BV _{DSS}	Q1 – Q4 MOSFET Drain-to-Source Breakdown Voltage The maximum drain-to-source voltage the MOSFET can endure without the avalanche breakdown of the body- drain P-N junction in off state. The measurement conditions are to be found in Table 5. The typ. Temperature behavior is described in Figure 13
V _{GS(th)}	Q1 – Q4 MOSFET Gate to Source Threshold Voltage The gate-to-source voltage measurement is triggered by a threshold ID current given in conditions at Table 11. The typ. Temperature behavior can be found in Figure 12
R _{DS(ON)}	Q1 – Q4 MOSFET On Resistance RDS(on) is the total resistance between the source and the drain during the on state. The measurement conditions are to be found in Table 5.} The typ behavior can be found in Figure 10 and Figure 11 as well as Figure 17
9FS	Q1 – Q4 MOSFET Forward Transconductance Transconductance is the gain in the MOSFET, expressed in the Equation below. t describes the change in drain current by the change in the gate–source bias voltage: $g_{fs} = [-\Delta I_{DS} / \Delta V_{GS}]_{VDS}$
I _{GSS}	Q1 – Q4 MOSFET Gate-to-Source Leakage Current The current flowing from Gate to Source at the maximum allowed VGS The measurement conditions are described in the Table 5.
I _{DSS}	Q1 – Q4 MOSFET Drain-to-Source Leakage Current Drain – Source current is measured in off state while providing the maximum allowed drain-to-source voltage and the gate is shorted to the source. IDSS has a positive temperature coefficient.




Figure 3. Timing Measurement Variable Definition

Table 8. PARAMETER OF SWITCHING CHARACTERISTICS

Turn-On Delay (t _{d(on)}):	This is the time needed to charge the input capacitance, Ciss, before the load current ID starts flowing. The measurement conditions are described in the Table 5. For signal definition please check Figure 3 above.
Rise Time (t _r):	The rise time is the time to discharge output capacitance, Coss. After that time the MOSFET conducts the given load current ID. The measurement conditions are described in the Table 5. For signal definition please check Figure 3 above.
Turn-On Time (ton):	Is the sum of turn-on-delay and rise time
Turn-Off Delay (t _{d(off)}):	td(off) is the time to discharge Ciss after the MOSFET is turned off. During this time the load current ID is still flowing The measurement conditions are described in the Table 5. For signal definition please check Figure 3 above.
Fall Time (t _f):	The fall time, tf, is the time to charge the output capacitance, Coss. During this time the load current drops down and the voltage VDS rises accordingly. The measurement conditions are described in the Table 5. For signal definition please check Figure 3 above.
Turn-Off Time (t _{off}):	Is the sum of turn-off-delay and fall time

TYPICAL CHARACTERISTICS




Figure 4. Normalized Power Dissipation vs. Case Temperature




Figure 5. Maximum Continuous I_D vs. Case Temperature




Figure 6. Transfer Characteristics




Figure 7. Forward Diode




Figure 8. Saturation (25°C)





Figure 9. Saturation (150°C)


TYPICAL CHARACTERISTICS (continued)



2.5 ID = 20 A VGS = 10 V QBY 1.0 QB

Figure 10. On-Resistance vs. Gate-to-Source Voltage

Figure 11. R_{DS(norm)} vs. Junction Temperature







Figure 12. Normalized V_{th} vs. Temperature

Figure 13. Breakdown Voltage vs. Temperature






Figure 14. Eoss vs. Drain-to-Source Voltage

Figure 15. Capacitance Variation

TYPICAL CHARACTERISTICS (continued)




Figure 16. Gate Charge

Figure 17. R_{DS(ON)} vs. I_D




Figure 18. Safe Operating Area

Figure 19. Peak Current Capability





Figure 20. Transient Thermal Impedance

ORDERING INFORMATION

Part Number	Package	Lead Forming	Snubber Capacitor Inside	DBC Material	Pb-Free and RoHS Compliant	Operating Temperature (T _A)	Packing Method
NXV65HR82DS1	APM16-CAA	Y-Shape	Yes	Al ₂ O ₃	Yes	–40°C∼125°C	Tube
NXV65HR82DS2	APM16-CAB	L-Shape	Yes	Al ₂ O ₃	Yes	–40°C∼125°C	Tube
NXV65HR82DZ1	APM16-CAA	Y-Shape	No	Al ₂ O ₃	Yes	–40°C∼125°C	Tube
NXV65HR82DZ2	APM16-CAB	L-Shape	No	Al ₂ O ₃	Yes	-40°C~125°C	Tube

DATE 08 OCT 2020



NOTES:

- 1. DIMENSIONING AND TOLERANCING PER. ASME Y14.5M, 2009.
- 2. CONTROLLING DIMENSION: MILLIMETERS
- 3. DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.

	MILLIMETERS				
DIM	MIN.	NOM.	MAX.		
A2	4.30	4.50	4.70		
b	0.45	0.50	0.60		
b2	1.15	1.20	1.30		
С	0.45	0.50	0.60		
D	39.90	40.10	40.30		
Е	33.80	34.30	34.80		
E1	21.70	21.90	22.10		
E2	12.10	12.30	12.50		
е	1.478	1.778	2.078		
e1	2.20	2.50	2.80		
L	12.10	12.40	12.70		
L1	4.80 REF				
L2	7.30	7.60	7.90		
q	36.85	37.10	37.35		
S	3.159 REF				
ØΑ	2.95	3.20	3.45		

GENERIC MARKING DIAGRAM*

BOTTOM VIEW

XXXXXXXXXXXXXXX **ZZZ ATYWW** NNNNNN

XXXX = Specific Device Code


ZZZ = Lot ID

ΑT = Assembly & Test Location


Υ = Year W = Work Week NNN = Serial Number *This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "■", may or may not be present. Some products may not follow the Generic Marking.


DOCUMENT NUMBER:	98AON94732G	Electronic versions are uncontrolled except when accessed directly from the Document Repos Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	APMCA-A16 / 16LD, AUTOMOTIVE MODULE		PAGE 1 OF 1	


ON Semiconductor and un are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.



DATE 03 NOV 2020







NOTES:

- 1. DIMENSIONING AND TOLERANCING PER. ASME Y14.5M, 2009.
- 2. CONTROLLING DIMENSION; MILLIMETERS
- DIMENSIONS ARE EXCLUSIVE OF BURRS, MOLD FLASH AND TIE BAR EXTRUSIONS.

	MILLIMETERS				
DIM	MIN.	NOM.	MAX.		
A2	4.30	4.50	4.70		
b	0.45	0.50	0.60		
b2	1.15	1.20	1.30		
С	0.45	0.50	0.60		
D	39.90	40.10	40.30		
Е	26.20	26.70	27.20		
E1	21.70	21.90	22.10		
E2	12.10	12.30	12.50		
е	1.478	1.778	2.078		
e1	2.20	2.50	2.80		
L	9.20	9.55	9.90		
L1	5.05 REF				
q	36.85	37.10	37.35		
S	3.159 REF				
ØΑ	2.95 3.20 3.45				

GENERIC MARKING DIAGRAM*

XXXX = Specific Device Code

ZZZ = Lot ID

AT = Assembly & Test Location

Y = Year W = Work Week

NNN = Serial Number

*This information is generic. Please refer to device data sheet for actual part marking. Pb-Free indicator, "G" or microdot "•", may or may not be present. Some products may not follow the Generic Marking.

DOCUMENT NUMBER:	98AON97133G	Electronic versions are uncontrolled except when accessed directly from the Document Repositor Printed versions are uncontrolled except when stamped "CONTROLLED COPY" in red.		
DESCRIPTION:	APMCA-B16 / 16LD, AUTOMOTIVE MODULE		PAGE 1 OF 1	

ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. ON Semiconductor does not convey any license under its patent rights nor the rights of others.

onsemi, ONSEMi., and other names, marks, and brands are registered and/or common law trademarks of Semiconductor Components Industries, LLC dba "onsemi" or its affiliates and/or subsidiaries in the United States and/or other countries. onsemi owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of onsemi's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. Onsemi reserves the right to make changes at any time to any products or information herein, without notice. The information herein is provided "as-is" and onsemi makes no warranty, representation or guarantee regarding the accuracy of the information, product features, availability, functionality, or suitability of its products for any particular purpose, nor does onsemi assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using onsemi products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications provided by onsemi. "Typical" parameters which may be provided in onsemi data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. onsemi does not convey any license under any of its intellectual property rights nor the rights of others. onsemi products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer p

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:
Email Requests to: orderlit@onsemi.com

onsemi Website: www.onsemi.com

TECHNICAL SUPPORT North American Technical Support: Voice Mail: 1 800-282-9855 Toll Free USA/Canada Phone: 011 421 33 790 2910

Europe, Middle East and Africa Technical Support:

Phone: 00421 33 790 2910

For additional information, please contact your local Sales Representative