



■ Specifications :


- Voltage rating: 125V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X2004 H- XX-N0
① ② ③ ④

- ① Series Number
- ② Category : H-HSG
- ③ Row No.Pin No:xx-02-16P
- ④ Material:N0-PA66;



Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	6.00	4.80	10	18.00	22.00	20.80
03	4.00	8.00	6.80	11	20.00	24.00	22.80
04	6.00	10.00	8.80	12	22.00	26.00	24.80
05	8.00	12.00	10.80	13	24.00	28.00	26.80
06	10.00	14.00	12.80	14	26.00	30.00	28.80
07	12.00	16.00	14.80	15	28.00	32.00	30.80
08	14.00	18.00	16.80	16	30.00	34.00	32.80
09	16.00	20.00	18.80				



PARTY NO	Material	Suitable XKB Terminal	Suitable XKB Terminal
X2004H-XX-N0	PA66 UL 94V-0	X2004T	X2004W

广东星坤科技股份有限公司

生效

MARK	DESCRIPTION	DATE	REVISED	APPROVED
ΔX				
ΔX				
ΔX				

REVISIONS	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X2004H-XX-N0
CHKD	DATE	UNIT: mm/in	PART NO.: 2.0mm Crimp Style Connectors
APPD	DATE	SIZE: A4	DWG NO.:
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT: 1.0g
			SHEET: 1/1
			REVISION: A0

文件工程章

www.xk-dg.cn www.helloxkb.com www.helloxkb.cn