



■ Specifications :

- Voltage rating: 125V AC / DC
- Current rating: 3A AC / DC
- Withstanding voltage: 1000V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000M Ω
- Contact resistance: ≤10mΩ
- After environmental testing : ≤20mΩ

X2004 W R-XX- N0 SN
① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category : W-WAFER
- ③ Wedding Board Angle : R-Stright 90°
- ④ Row No.-Pin No.: XX-02P~16P
- ⑤ Material : NO-PA66 94V-0
- ⑥ Plating Category: Sn-Bright Tin Plating

Poles	Dimensions(mm)			Poles	Dimensions(mm)		
	A	B	C		A	B	C
02	2.00	5.96	4.96	10	18.00	21.96	20.96
03	4.00	7.96	6.96	11	20.00	23.96	22.96
04	6.00	9.96	8.96	12	22.00	25.96	24.96
05	8.00	11.96	10.96	13	24.00	27.96	26.96
06	10.0	13.96	12.96	14	26.00	29.96	28.96
07	12.0	15.96	14.96	15	28.00	31.96	30.96
08	14.0	17.96	16.96	16	30.00	33.96	32.96
09	16.0	19.96	18.96				

X2004WR-XX-N0SN	Nyolin 66 UL 94V-0	Brass	Tin-Plated	X2004H
PART NO	Material	Material(pin)	Finish(pin)	Suitable XKTB Terminal

广东星坤科技股份有限公司
Recommended C.B Layout
General Tolerance±0.05

生效	ΔX	日期						ANGLAR	±5°
	ΔX							L ≤ 4	±0.2
	ΔX							4 < L ≤ 16	±0.3
	MARK	DESCRIPTION	DATE	REVISED	APPROVED			16 < L ≤ 63	±0.4
REVISIONS								L > 63	±0.5
UNSPECIFIED TOLERANCES									

DSND	DATE	SCALE: N/A	MODEL TYPE: X2004WR-XX-N0SN
DWN	DATE	VIEW:	PART NO.: 2.0mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

文件工程章