



X2510 W V X- XX SP- N0SN XX

① ②③④⑤ ⑥ ⑦⑧⑨

- ① Series No.
- ② Category:  
W-wafer
- ③ Welding Board Angle:  
R90
- ④ Welding Way:  
Blank-DIP
- ⑤ Row No.-Pin No.  
XX-Single row
- ⑥ Special NO.  
SP-Short back
- ⑦ Material:  
NO-PA66 94V-0

Planting Category:

- V-All Gold-Plated
- 01-Gold Flash 02-2U 03-3U 05-5U
- 10-10U 15-15U 30-30U 50-50U
- SN-Bright tin plating 70-120U
- SN-Bright tin plating 120U Min
- SW-Fog Tin plating

- ⑧ Color:  
Blank-natural color

Specifications:

规格:  
Voltage rating:250V AC/DC  
额定电压: 250V AC/DC  
Current rating:  
额定电流:  
Withstanding voltage: 800V AC/minute  
耐压电压: 800V AC/minute  
Temperature range:-25℃~+85℃  
温度范围: -25℃~+85℃  
Insulation resistance:≥1000MΩ  
绝缘电阻: ≥1000MΩ  
Contact resistance: ≤10mΩ  
接触电阻:≤10mΩ  
After environment testing: ≤20mΩ  
环境试验后: ≤20mΩ

Poles	Dimensions (mm)	
	A	B
2	2.54	5.08
3	5.08	7.62
4	7.62	10.16
5	10.16	12.70
6	12.70	15.24
7	15.24	17.78
8	17.78	20.32
9	20.32	22.86
10	22.86	25.40
11	25.40	27.94
12	27.94	30.48
13	30.48	33.02
14	33.02	35.56
15	35.56	38.10
16	38.10	40.64
17	40.64	43.18
18	43.18	45.72
19	45.72	48.26
20	48.26	50.80

X2510WV-XXSP-N0SN	Nylon 66 UL94V-0	Brass	Tin-Plated	X2510H
PART NO	Material	Material(Pin)	Finist(Pin)	

REVISIONS					UNSPECIFIED TOLERANCES			XKB INDUSTRIAL PRECISION CO.,LIMITED			
ΔX					ANGLAR	±5°	DSND		DATE	SCALE: N/A	MODEL TYPE:
ΔX					L ≤ 4	±0.2	DWN		DATE	VIEW:	PART NO.:
ΔX					4 < L ≤ 16	±0.3	CHKD		DATE	UNIT: mm/in	2.54 mm Crimp Style Connectors
MARK	DESCRIPTION	DATE	REVISED	APPROVED	16 < L ≤ 63	±0.4	APPD		DATE	SIZE: A4	DWG NO.:
					L > 63	±0.5					X2510WV-XXSP-N0SN
											WEIGHT
											SHEET
											REVISION
											1.0g
											1/1
											A0