



FEATURES

- Light operating force
- Long term low contact resistance
- Momentary or latching operation
- Short stroke 1.5mm to latch
- Compact spacing on PCB of 5.8mm

SPECIFICATIONS

1.ELECTRICAL	
● Contact rating	0.1A, 30VDC
● Contact resistance	50mWMax.
● Insulation resistance	100MΩMin. at 250VDC
● Dielectric strength	250VAC Min. for 60 sec.
2.MECHANICAL AND ENVIRONMENTAL	
● Temperature rating	Operation: -15 °C to +55 °C Storage: -25 °C to +65 °C
● Operation force	160±80gf
● Stroke	Lock Stroke: 1.5±0.2mm Full Stroke: 2.0±0.2mm
● Operation life	full load: 1x10 ⁴ Cycles no load: 1x10 ⁵ Cycles
● Contact form	DPDT

PAPT NO	XKB5858-X-C
OPERATION	W:NO LOCK Z:LOCK

ITEM	PAPT NAMF	TER,NO	QTY	MATERIAL	FINISHING	REMARK
⑦	Contact	—	1	Phosphor bronze	Plating silvering	—
⑥	Terminal	—	3	Brass	Plating silvering	—
⑤	Spring	—	1	Sus	Natural	—
④	Base	—	1	Nylon	—	—
③	Crochet Needle	—	1	Sus	Natural	—
②	Cover	—	1	Nylon	—	—
①	Keystake	—	1	Nylon	—	—

广东星坤科技股份有限公司

生 ΔX 日期
效 ΔX 日期
MARK

文件工程章

REVISIONS	UNSPECIFIED TOLERANCES	DSND	DATE	SCALE: N/A	MODEL TYPE:
DESCRIPTION <td>ANGULAR ±5°</td> <td>DWN</td> <td>DATE</td> <td>VIEW: </td> <td>KEY SWITCH</td>	ANGULAR ±5°	DWN	DATE	VIEW:	KEY SWITCH
DATE	X.X ±0.2mm	CHKD	DATE	UNIT: mm/in	PART NO.:
REVISED	X.XX ±0.1mm	APPD	DATE	SIZE: A4	DWG NO.:
APPROVED	X.XXX ±0.05mm	XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT
					SHEET
					REVISION
					1.0g
					1/1
					A0