



- Specifications:**
- Voltage rating: 250V AC/DC
  - Current rating: 3A AC/DC
  - Withstanding voltage: 1500V AC/minute
  - Temperature range: -40 °C ~ +105 °C
  - Insulation resistance: ≥500MΩ
  - Contact resistance: ≤10mΩ
  - After environmental testing: ≤20mΩ

X2521 H F-XX G-N0

① ② ③ ④ ⑤ ⑥

- ① Series No.
- ② Category: H-HSG
- ③ Welding Board Angle: F-Female HSG
- ④ Row No -pin No.: XX-02P~12P
- ⑤ Plug the pin & Special No.: G-With Ears
- ⑥ Material: NO-PA66 94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	8.00	08	17.50	23.00
03	5.00	10.50	09	20.00	25.50
04	7.50	13.00	10	22.50	28.00
05	10.00	15.50	11	25.00	30.50
06	12.50	18.00	12	27.50	33.00
07	15.00	20.50			

X2521HF-XXG-N0	Black	PA66 UL 94V-0	Brass	Tin-Plated	X2521HM-G
PART NO	Color	Material	Material(Pin)	Finish(Pin)	Suitable KKB Terminal

ΔX				KKB	ANGLAR	±5°
ΔX					L ≤ 4	±0.2
ΔX					4 < L ≤ 16	±0.3
ΔX					16 < L ≤ 63	±0.4
MARK					L > 63	±0.5
REVISIONS						
UNSPECIFIED TOLERANCES						

DSND	DATE	SCALE: N/A	MODEL TYPE:
DWN	DATE	VIEW:	X2531HF-XXG-N0
CHKD	DATE	UNIT: mm/in	PART NO.:
APPD	DATE	SIZE: A4	DWG NO.:

www.hellokko.com

KKB INDUSTRIAL PRECISION CO., LIMITED

WEIGHT	SHEET	REVISION
1.0g	1/1	A0