





Poles	Applicable panel thickness mm					
	0.5-0.9	1.0-1.5	1.5-2.0	C	D	D
02	5.7	9.6	5.7	9.8	5.7	10.0
03	8.2	12.1	8.2	12.3	8.2	12.5
04	10.7	14.6	10.7	14.8	10.7	15.0
05	13.2	17.1	13.2	17.3	13.2	17.5
06	15.7	19.6	15.7	19.8	15.7	20.0
07	18.2	22.1	18.2	22.3	18.2	22.5
08	20.7	24.6	20.7	24.8	20.7	25.0
09	23.2	27.1	23.2	27.3	23.2	27.5
10	25.7	29.6	25.7	29.8	25.7	30.0
11	28.2	32.1	28.2	32.3	28.2	32.5
12	30.7	34.6	30.7	34.8	30.7	35.0



- Specifications:**
- Voltage rating: 250V AC/DC
 - Current rating : 3A AC/DC
 - Withstanding voltage: 1500V AC/minute
 - Temperature range: -40 °C ~ +105 °C
 - Insulation resistance: ≥500MΩ
 - Contact resistance: ≤10mΩ
 - After environmental testing: ≤20mΩ
- X2521 H M- XX G-NO
 ① ② ③ ④ ⑤ ⑥
- ① Series No.
 - ② Category: H-HSG
 - ③ Welding Board Angle: M-male HSG
 - ④ Row No. -pin No.: XX-02P~12P
 - ⑤ Plug the pin & Special No.: Mating X2521HF-G
 - ⑥ Material: N0-PA66 94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
02	2.50	5.50	08	17.50	20.50
03	5.00	8.00	09	20.00	23.00
04	7.50	10.50	10	22.50	25.50
05	10.00	13.00	11	25.00	28.00
06	12.50	15.50	12	27.50	30.50
07	15.00	18.00			

X2521HM-XXG-NO	Black	PA66 UL 94V-0	Brass	Tri-Plated	X2521HF-G
PART NO	Color	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

ΔX	ΔX	ΔX	MARK	DESCRIPTION	DATE	REVISED	APPROVED	UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: X2531HM-XXG-NO
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	