



XKB




Circuit 1


4P-24P




4P-24P




2P




3P



2P



3P



Recomm and PCB Layout

Specificationsxkb

规格:

Voltage rating:250V AC/DC

额定电压: 250V AC/DC

Current rating:3A AC/DC

额定电流: 3A AC/DC XKB

Withstanding voltage:1500V AC/minute

耐受电压: 1500V AC/分钟

Temperature range:-25℃~+85℃

温度范围: -25℃~+85℃

Insulation resistance:≥1000MΩ

绝缘电阻: ≥1000MΩ

Contact resistance:≤20mΩ

接触电阻: ≤20mΩ XKB

After environmental testing:≤30mΩ

环境测试后: ≤30兆欧

X9556 WR XX-XX X-NDV01 XX

- ① Series No.
- ② Category
- ③ W-wafer
- ④ Welding Board Angle
- ⑤ Pitch
- ⑥ Welding Way
- ⑦ Blank-DIP
- ⑧ Row No-Pin No
- ⑨ XX-Single row
- ⑩ Special NO.
- ⑪ Material
- ⑫ NI-PA66 94V-0
- ⑬ Plating Category
- ⑭ All Gold-Plated
- ⑮ "01-1u" *02-2u" *03-3u" *05-5u"
- ⑯ "10-10u" *15-15 u" *30-30u" *50-50u"
- ⑰ SW-Bright tin plating 70u"
- ⑱ SW-Bright tin plating 100u"Min.
- ⑲ SW-Fog Tin plating
- ⑳ Color
- ㉑ Blank-natural color

Poles	Dimensions (mm)	
	A	B
2	2.54	7.62
3	5.08	10.16
4	7.62	12.70
5	10.16	15.24
6	12.70	17.78
7	15.24	20.32
8	17.78	22.86
9	20.32	25.40
10	22.86	27.94
11	25.40	30.48
12	27.94	33.02
13	30.48	35.56
14	33.02	38.10
15	35.56	40.64
16	38.10	43.18
17	40.64	45.72
18	43.18	48.26
19	45.72	50.80
20	48.26	53.34
21	50.80	55.88
22	53.34	58.42
23	55.88	60.96
24	58.42	63.50

X9556WR-XX-NDV01	Nylon 66 UL 94V-0	Brass	Gold-Flash	X9556H
PART NO	Material	Material(Pin)	Finish(Pin)	Suitable XKB Terminal

广东星坤科技股份有限公司

生 日期

文件工程章

REVISIONS

www.heloxkb.com

	XKB	ANGLAR	±5°
		L ≤ 4	±0.2
		4 < L ≤ 16	±0.3
		16 < L ≤ 63	±0.4
		L > 63	±0.5

DSND	DATE	SCALE: NA	MODEL TYPE: X9556WR-XX-NDV01
DWN	DATE	VIEW:	PART NO.: 2.54 mm Crimp Style Connectors
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO., LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0