



Specifications

- Voltage rating: 250V AC / DC
- Current rating: 5A AC / DC
- Withstanding voltage: 1500V AC/minute
- Temperature range: -40°C~+105°C
- Insulation resistance: ≥1000MΩ
- Contact resistance: ≤10mΩ
- After environmental testing: ≤20mΩ

X3025 WR X - XX X - X X SN XX
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨

- ① Series No.
- ② Category : W-wafer
- ③ Welding Board Angle: R-90°
- ④ Welding Way: Blank-DIP
- ⑤ Row No.-Pin No.: XX-Single row
- ⑥ Plug the Pin & Special No.:
- ⑦ Material :
LP-LCP 94V-0 N0-PA9T 94V-0
- ⑧ Planting Category:
SN-Bright tin plating 70u" Min.
- ⑨ Color : Blank-Natural Color Black

Poles	Dimension s(mm)			Poles	Dimensions(mm)		
	AB	C			AB	C	
01	---	6.65	---	07	18.00	24.65	13.70
02	3.00	9.65	---	08	21.00	27.65	16.70
03	6.00	12.65	---	09	24.00	30.65	19.70
04	9.00	15.65	4.70	10	27.00	33.65	22.70
05	12.00	18.65	7.70	11	30.00	36.65	25.70
06	15.00	21.65	10.70	12	33.00	39.65	28.70

X3025 WR-XX-N0SNXX	PA9T UL 94V-0	Brass	Tin-Plated	X3025H	
X3025WR-XX-LPSNXX	LCP UL 94V-0				
PART NO	Material	Material(Pin)	Finish(Pin)	Mates With	XXKB Housing

DSND	DATE	SCALE: NA	MODEL TYPE: X3025WR-XX-N0SN
DWNN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.:
APPD	DATE	SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED			WEIGHT 1.0g
			SHEET 1/1
			REVISION A0

Recommended P.C.B Layout
 General Tolerances±0.05

			XKB	ANGLR	±5°
				L ≤ 4	±0.2
				4 < L ≤ 16	±0.3
				16 < L ≤ 63	±0.4
				L > 63	±0.5
UNSPECIFIED TOLERANCES					

REVISIONS
 www.heloxkb.com

广东星坤科技股份有限公司

生 日期
 發 日期

文件工程章
 REVISIONS
 www.heloxkb.com