



3D VIEW

NOTES:

- 1.MATERIAL: SEE "TABLE 1";
- 2.FINISH: SEE "TABLE 1";
- 3.ELECTRICAL:
  - 3.1. VOLTAGE RATING: 12 VAC RMS.
  - 3.2. CURRENT RATING: 0.5 AMP.
  - 3.3. CONTACT RESISTANCE: 50mΩ Max.(Initial), 100mΩ Max.(After Life test).
  - 3.4. INSULATION RESISTANCE:100 MΩ Min,500VDC.(Initial), 50 MΩ Min,500VDC.(After Humidity test).
  - 3.5. WITHSTAND VOLTAGE: 500 VAC RMS 50(60)Hz,1 minute
4. MECHANICAL:
  - 4.1. MATING FORCE: 3.0Kgf MAX.
  - 4.2. UNmating FORCE: 0.3Kgf MIN.
  - 4.3. OPERATING LIFE: 5000 CYCLES MIN.
- 5.ENVIRONMENTAL:
  - 5.1. OPFRATION: -30°C~+80°C.



	MATERIAL	PLATING
terminal 1	Phosphor Bronze	Gold
terminal 2	Phosphor Bronze	Gold
terminal 3	Phosphor Bronze	Gold
terminal 4	Phosphor Bronze	Gold
terminal 5	Phosphor Bronze	Gold
terminal 6	Phosphor Bronze	Gold
plastic	High Temp. Thermoplastic	

广东星坤科技股份有限公司

Color B:Black W: White

生效日期

MARK	DESCRIPTION	DATE	REVISED	APPROVED
文件工程章				

ANGLAR	±5°
L ≤ 4	±0.2
4 < L ≤ 16	±0.3
16 < L ≤ 63	±0.4
L > 63	±0.5

UNSPECIFIED TOLERANCES

DSND	DATE	SCALE: N/A	MODEL TYPE: 3.5 PHONE JACK
DWN	DATE	VIEW:	PART NO.:
CHKD	DATE	UNIT: mm/in	DWG NO.: PJ-38647-X
APPD	DATE	SIZE: A4	WEIGHT 1.0g SHEET 1/1 REVISION A0

XKB INDUSTRIAL PRECISION CO., LIMITED