




Specifications:

- Voltage rating:250V AC/DC
- Current rating : 3 A AC/DC
- Withstanding voltage:1000V AC/minute
- Temperature range:-25 °C ~+85 °C
- Insulation resistance:≥1000MΩ
- Contact resistance:≤10mΩ
- After environmental testing:≤20mΩ



X9555 H - 2*XXB3 -N0

① ② ③ ④ ⑤

- ① Series No.
- ② Category:H-HSG
- ③ Row No.-pin No.:2*XX-02P~32P
- ④ B3:With wings
- ⑤ Material:N0-PA66 94V-0

Poles	Dimensions(mm)		Poles	Dimensions(mm)	
	A	B		A	B
2*02	2.54	18.56	2*18	43.18	59.20
2*03	5.08	21.10	2*19	45.72	61.74
2*04	7.62	23.64	2*20	48.26	64.28
2*05	10.16	26.18	2*21	50.80	66.82
2*06	12.70	28.72	2*22	53.34	69.36
2*07	15.24	31.26	2*23	55.88	71.90
2*08	17.78	33.80	2*24	58.42	74.44
2*09	20.32	36.34	2*25	60.96	76.98
2*10	22.86	38.88	2*26	63.50	79.52
2*11	25.40	41.42	2*27	66.04	82.06
2*12	27.94	43.96	2*28	68.58	84.60
2*13	30.48	46.50	2*29	71.12	87.14
2*14	33.02	49.04	2*30	73.66	89.69
2*15	35.56	51.58	2*31	76.20	92.22
2*16	38.10	54.12	2*32	78.74	94.76
2*17	40.64	56.66			

X9555H-2*XXB3-N0	PA66 UL 94V-0	X9555T	X9555W
PART NO	Material	Suitable XKB Terminal	Suitable XKB Terminal

MARK	DESCRIPTION	DATE	REVISED	APPROVED	XKB	ANGLAR	±5°
Δx						L ≤ 4	±0.2
Δx						4 < L ≤ 16	±0.3
Δx						16 < L ≤ 63	±0.4
						L > 63	±0.5
UNSPECIFIED TOLERANCES							
REVISIONS							
www.helloxkb.com							

DSND		DATE		SCALE: N/A	MODEL TYPE: X9555H-2*XXB3-N0
DWN		DATE		VIEW:	PART NO.:
CHKD		DATE		UNIT: mm/in	DWG NO.:
APPD		DATE		SIZE: A4	
XKB INDUSTRIAL PRECISION CO.,LIMITED					WEIGHT 1.0g
					SHEET 1/1
					REVISION A0