

Inductor



Figure



Type A



Type B



Type C

Note: The image shown here is indicative only. If there is inconsistency between the image and the actual product, the actual product shall govern.

Specifications:

<u>SERIES : SKPC-ERCB13-XXX</u>	
Test Conditions:	25°C 10KHz 1V
Inductance :	13μH±5% (No Current)
Dimensions(L*W*H):	43*33*13mm
Pins and Connection	2*Terminals
Hi-Pot(Wire to Core)	1KV/3KV/5KV DC^①

Model	Type	DCR Max 20°C	Isat L drops 20% (Max)	Irms Temperature Rise 40°C (Max.) @	Weight (Max)
SKPC-ERCB13-4B(135)	B	3.4mΩ	15A	9.6A	47g
SKPC-ERCB13-5C(135)	C	2.6mΩ	19A	9.6A	59g
SKPC-ERCB13-6C(135)	C	3.3mΩ	24A	9.6A	63g
SKPC-ERCB13-7C(135)	C	8.4mΩ	27A	4.8A	53g
SKPC-ERCB13-8C(135)	C	9.4mΩ	32A	4.8A	55g
SKPC-ERCB13-9C(135)	C	10.4mΩ	38A	4.8A	55g
SKPC-ERCB13-10C(135)	C	11.5mΩ	42A	4.8A	57g
SKPC-ERCB13-11C(135)	C	12.9mΩ	47A	4.8A	57g
SKPC-ERCB13-12C(135)	C	14.1mΩ	52A	4.8A	57g

Operating temperature: -40°C to +75°C

Inductor



Note:


1. Classification of different Hi-Pot level : **1-1KVDC/3-3KVDC/5-5KVDC**
2. Since different ways of heat dissipation affect Temperature rise, Temperature rise is reference.

Material List


No.	Item	Material Description
1	Core	Ferrite
2	Wire	Copper
3	Solder (Lead Free)	SnAg3%Cu
4	Insulation	Polyimide+Polyamide-imide Resin

Note: Temperature tolerance grade: **H CLASS**

Schematic Diagram



Configurations and Dimensions (mm)






Inductor







Model.	Type	Description of pins
SKPC-ERCB13-4B(135)	B	PIN1+PIN5
SKPC-ERCB13-5C(135)	C	PIN2+PIN7
SKPC-ERCB13-6C(135)	C	PIN2+PIN8
SKPC-ERCB13-7C(135)	C	PIN1+PIN8
SKPC-ERCB13-8C(135)	C	PIN1+PIN9
SKPC-ERCB13-9C(135)	C	PIN1+PIN8
SKPC-ERCB13-10C(135)	C	PIN1+PIN9
SKPC-ERCB13-11C(135)	C	PIN1+PIN8
SKPC-ERCB13-12C(135)	C	PIN1+PIN9



L(uH) vs Frequency(KHz)



Inductor




Inductor






Note: This data is based on the WK-3260B.




L(uH) vs Current(A)





Inductor



Inductor



Inductor



Note: This data is based on the DPG10 Power Choke Tester.