

# Inductor



## Figure



Type A



Type B



Type C

Note: The image shown here is indicative only. If there is inconsistency between the image and the actual product, the actual product shall govern.

## Specifications:

<b><u>SERIES : SKPC-ERDA2.5-XXX</u></b>	
Test Conditions:	25°C 10KHz 1V
Inductance :	2.5μH±5% (No Current)
Dimensions(L*W*H):	54*42*16mm
Pins and Connection	2*Terminals
Hi-Pot(Wire to Core)	1KV/3KV/5KV DC <sup>①</sup>

Model	Type	DCR Max 20°C	Isat L drops 20% (Max)	Irms Temperature Rise 40°C (Max.) <sup>②</sup>	Weight (Max)
SKPC-ERDA2.5-2A(135)	A	0.3mΩ	72A	72A	116g
SKPC-ERDA2.5-3B(135)	B	0.8mΩ	124A	38.4A	115g
SKPC-ERDA2.5-4B(135)	B	1.3mΩ	177A	28.8A	115g

Operating temperature: -40°C to +75°C

Note:

1. Classification of different Hi-Pot level : 1-1KVDC/3-3KVDC/5-5KVDC
2. Since different ways of heat dissipation affect Temperature rise, Temperature rise is reference.

# Inductor




## Material List


No.	Item	Material Description
1	Core	Ferrite
2	Wire	Copper
3	Solder (Lead Free)	SnAg3%Cu
4	Insulation	Polyimide+Polyamide-imide Resin

Note: Temperature tolerance grade: **H CLASS**

## Schematic Diagram



## Configurations and Dimensions (mm)






Model.	Type	Description of pins
SKPC-ERDA2.5-2A(135)	A	PIN1+PIN3
SKPC-ERDA2.5-3B(135)	B	PIN1+PIN4
SKPC-ERDA2.5-4B(135)	B	PIN1+PIN5

# Inductor



## L(uH) vs Frequency(KHz)






Note: This data is based on the WK-3260B.

# Inductor



L( $\mu$ H) vs Current(A)



Note: This data is based on the DPG10 Power Choke Tester.