

Inductor



Figure



Type A



Type B



Type C

Note: The image shown here is indicative only. If there is inconsistency between the image and the actual product, the actual product shall govern.

Specifications:

<u>SERIES : SKPC-ERDA25-XXX</u>	
Test Conditions:	25°C 10KHz 1V
Inductance :	25μH±5% (No Current)
Dimensions(L*W*H):	54*42*16mm
Pins and Connection	2*Terminals
Hi-Pot(Wire to Core)	1KV/3KV/5KV DC①

Model	Type	DCR Max 20°C	Isat L drops 20% (Max)	Irms Temperature Rise 40°C (Max.) ②	Weight (Max)
SKPC-ERDA25-4B(135)	B	4.0mΩ	11A	9.6A	90g
SKPC-ERDA25-5C(135)	C	3.1mΩ	16A	9.6A	108g
SKPC-ERDA25-6C(135)	C	3.3mΩ	20A	9.6A	115g
SKPC-ERDA25-7C(135)	C	4.0mΩ	25A	9.6A	121g
SKPC-ERDA25-8C(135)	C	9.2mΩ	30A	4.8A	102g
SKPC-ERDA25-9C(135)	C	10.2mΩ	33A	4.8A	102g
SKPC-ERDA25-10C(135)	C	11.1mΩ	38A	4.8A	105g
SKPC-ERDA25-11C(135)	C	12.4mΩ	40A	4.8A	105g
SKPC-ERDA25-12C(135)	C	13.2mΩ	47A	4.8A	105g
SKPC-ERDA25-13C(135)	C	14.2mΩ	53A	4.8A	108g
SKPC-ERDA25-14C(135)	C	15.3mΩ	58A	4.8A	108g
SKPC-ERDA25-15C(135)	C	16.4mΩ	60A	4.8A	108g

Inductor



Operating temperature: -40°C to +75°C

Note:


1. Classification of different Hi-Pot level : 1-1KVDC/3-3KVDC/5-5KVDC
2. Since different ways of heat dissipation affect Temperature rise, Temperature rise is reference.

Material List


No.	Item	Material Description
1	Core	Ferrite
2	Wire	Copper
3	Solder (Lead Free)	SnAg3%Cu
4	Insulation	Polyimide+Polyamide-imide Resin

Note: Temperature tolerance grade: H CLASS

Schematic Diagram



Configurations and Dimensions (mm)





Inductor







Model.	Type	Description of pins
SKPC-ERDA25-4B(135)	B	PIN1+PIN5
SKPC-ERDA25-5C(135)	C	PIN2+PIN7
SKPC-ERDA25-6C(135)	C	PIN2+PIN8
SKPC-ERDA25-7C(135)	C	PIN2+PIN9
SKPC-ERDA25-8C(135)	C	PIN1+PIN9
SKPC-ERDA25-9C(135)	C	PIN1+PIN8
SKPC-ERDA25-10C(135)	C	PIN1+PIN9
SKPC-ERDA25-11C(135)	C	PIN1+PIN8
SKPC-ERDA25-12C(135)	C	PIN1+PIN9
SKPC-ERDA25-13C(135)	C	PIN1+PIN8
SKPC-ERDA25-14C(135)	C	PIN1+PIN9
SKPC-ERDA25-15C(135)	C	PIN1+PIN8





L(uH) vs Frequency(KHz)





Inductor



Inductor




Inductor






Note: This data is based on the WK-3260B.




L(uH) vs Current(A)






Inductor





Inductor



Inductor



Inductor



Note: This data is based on the DPG10 Power Choke Tester.