

CMOS Voltage Converters


The Intersil HT7660B and HT7660A are monolithic CMOS power supply circuits which offer unique performance advantages over previously available devices. The HT7660B performs supply voltage conversions from positive to negative for an input range of +1.5V to +10.0V resulting in complementary output voltages of -1.5V to - 10.0V and the HT7660A does the same conversions with an input range of +1.5V to +12.0V resulting in complementary output voltages of -1.5V to - 12.0V. Only 2 noncritical external capacitors are needed for the charge pump and charge reservoir functions. The HT7660B and HT7660A can also be connected to function as voltage doublers and will generate output voltages up to +18.6V with a +10V input.

Contained on the chip are a series DC supply regulator, RC oscillator, voltage level translator, and four output power MOS switches. A unique logic element senses the most negative voltage in the device and ensures that the output N-Channel switch source-substrate junctions are not forward biased. This assures latchup free operation.

The oscillator, when unloaded, oscillates at a nominal frequency of 10kHz for an input supply voltage of 5.0V. This frequency can be lowered by the addition of an external capacitor to the "OSC" terminal, or the oscillator may be overdriven by an external clock.

The "LV" terminal may be tied to GROUND to bypass the internal series regulator and improve low voltage (LV) operation. At medium to high voltages (+3.5V to +10.0V for the HT7660B and +3.5V to +12.0V for the HT7660A), the LV pin is left floating to prevent device latchup.

Pinouts



Features

- Simple Conversion of +5V Logic Supply to \pm 5V Supplies
- Simple Voltage Multiplication (VOUT = (-) nVIN)
- Typical Open Circuit Voltage Conversion Efficiency 99.9%
- Typical Power Efficiency 98%
- Wide Operating Voltage Range
 HT7660B1.5V to 10.0V
 -
 - HT7660A 1.5V to 12.0V
- HT7660A 100% Tested at 3V
- Easy to Use Requires Only 2 External Non-Critical Passive Components
- No External Diode Over Full Temp. and Voltage Range
- · Pb-Free Plus Anneal Available (RoHS Compliant)

Applications

- · On Board Negative Supply for Dynamic RAMs
- Localized µProcessor (8080 Type) Negative Supplies
- Inexpensive Negative Supplies
- Data Acquisition Systems



Absolute Maximum Ratings

Supply Voltage
HT7660B
HT7660A
and OSC Input Voltage0.3V to (V+ +0.3V) for V+ < 5.5V (Note
2) (V+ -5.5V) to (V+ +0.3V) for V+ > 5.5V Current into
LV (Note 2)
Duration (VSUPPLY \leq 5.5V) Continuous

Operating Conditions

Temperature Range

i omporataro i tango	
HT7660BC, HT7660AC	$\ldots \ldots 0^\circ C$ to $70^\circ C$
HT7660AI	40°C to 85°C

Thermal Information

Thermal Resistance (Typical, Note 1)	θJA (°C/W)	θJC (°C/W)
PDIP Package*	110	N/A
SOIC Package	160	N/A
Maximum Storage Temperature Range		C to 150°C
Maximum Lead Temperature (Soldering, 10s	s)	300°C
(SOIC - Lead Tips Only)		

*Pb-free PDIPs can be used for through hole wave solder processing only. They are not intended for use in Reflow solder processing applications.

CAUTION: Stresses above those listed in "Absolute Maximum Ratings" may cause permanent damage to the device. This is a stress only rating and operation of the device at these or any other conditions above those indicated in the operational sections of this specification is not implied.

NOTE:

1. θ JA is measured with the component mounted on an evaluation PC board in free air.

Electrical Specifications	HT7660B and HT7660A, V+ = 5V, TA = 25°C, COSC = 0, Test Ci	ircuit Figure 11
Electrical opeointoations		
	Liplana Otherwise Specified	

			HT7660B			HT7660A			
PARAMETER	SYMBOL	TEST CONDITIONS	MIN	ТҮР	MAX	MIN	ТҮР	MAX	UNITS
Supply Current	1+	RL = ∞	-	170	500	-	80	165	μA
Supply Voltage Range - Lo	VL+	$MIN \leq T_{\ensuremath{\boldsymbol{A}}} \leq MAX, \ R_{\ensuremath{\boldsymbol{L}}} = 10k\Omega, \ LV \ \text{to} \ GND$	1.5	-	3.5	1.5	-	3.5	V
Supply Voltage Range - Hi	VH+	$MIN \leq T_{\ensuremath{A}} \leq MAX, \ R_{\ensuremath{L}} = 10k\Omega, \ LV \ \text{to Open}$	3.0	-	10.0	3	-	12	V
Output Source Resistance	OUT	IOUT = 20mA, TA = 25°C	-	55	100	-	60	100	Ω
		$IOUT = 20mA, 0^{\circ}C \le TA \le 70^{\circ}C$	-	-	120	-	-	120	Ω
		IOUT = 20mA, -55°C ≤ TA ≤ 125°C	-	-	150	-	-	-	Ω
		IOUT = 20mA, -40°C ≤ TA ≤ 85°C	-	-	-	-	-	120	Ω
		V^{+} = 2V, IOUT = 3mA, LV to GND	-	-	300	-	-	300	Ω
		$0^{\circ}C \le T_{A} \le 70^{\circ}C$							
		V + = 2V, I_{OUT} = 3mA, LV to GND,	-	-	400	-	-	-	Ω
		-55°C ≤ T _A ≤ 125°C							
Oscillator Frequency	osc		-	10	-	-	10	-	kHz
Power Efficiency	EF	$R_L = 5k\Omega$	95	98	-	96	98	-	%
Voltage Conversion Efficiency	OUT EF	RL = ∞	97	99.9	-	99	99.9	-	%
Oscillator Impedance	OSC	V+ = 2V	-	1.0	-	-	1	-	MΩ
		V = 5V	-	100	-	-	-	-	kΩ
HT7660A, V+ = 3V, T _A = 25°C,	OSC = Free r	unning, Test Circuit Figure 11, Unless Othe	rwise S	pecifie	d				
Supply Current (Note 3)	1+	V+ = 3V, RL = ∞, 25°C	-	-	-	-	26	100	μA
		0°C < TA < 70°C	-	-	-	-	-	125	μA
		-40°C < TA < 85°C	-	-	-	-	-	125	μΑ
Output Source Resistance	K OUT	V+ = 3V, IOUT = 10mA	-	-	-	-	97	150	Ω
		0°C < T _A < 70°C	-	-	-	-	-	200	Ω
		-40°C < TA < 85°C		-	-	-	-	200	Ω
Oscillator Frequency (Note 3)	OSC	V+ = 3V (same as 5V conditions)		-	-	5.0	8		kHz
		0°C < TA < 70°C		-	-	3.0	-	-	kHz
		-40°C < TA < 85°C				3.0			kHz



Electrical Specifications


HT7660B and HT7660A, V+ = 5V, TA = 25° C, COSC = 0, Test Circuit Figure 11 Unless Otherwise Specified **(Continued)**

			ŀ	IT7660	В		HT7	7660A	
PARAMETER	SYMBOL	TEST CONDITIONS	MIN	TYP	MAX	MIN	ТҮР	MAX	UNITS
Voltage Conversion Efficiency	VOUTEFF	V+ = 3V, RL = ∞	-	-	-	99	-	-	%
		MIN A MAX	-	-	-	99	-	-	%
Power Efficiency	EFF	V+ = 3V, RL = 5kΩ	-	-	-	96	-	-	%
		MIN A MAX	-	-	-	95	-	-	%


NOTES:


- 2. Connecting any input terminal to voltages greater than V+ or less than GND may cause destructive latchup. It is recommended that no inputs from sources operating from external supplies be applied prior to "power up" of the HT7660B, HT7660A.
- 3. Derate linearly above 50°C by 5.5mW/°C.
- 4. In the test circuit, there is no external capacitor applied to pin 7. However, when the device is plugged into a test socket, there is usually a very small but finite stray capacitance present, of the order of 5pF.
- 5. The Intersil HT7660A can operate without an external diode over the full temperature and voltage range. This device will function in existing designs which incorporate an external diode with no degradation in overall circuit performance.

Functional Block Diagram



Typical Performance Curves (Test Circuit of Figure 11)







HT7660



Typical Performance Curves (Test Circuit of Figure 11) (Continued)





(Hz)

FIGURE 4. POWER CONVERSION EFFICIENCY AS A FUNCTION OF OSC. FREQUENCY




FIGURE 6. UNLOADED OSCILLATOR FREQUENCY AS A FUNCTION OF TEMPERATURE





FIGURE 8. SUPPLY CURRENT AND POWER CONVERSION EFFICIENCY AS A FUNCTION OF LOAD CURRENT




Typical Performance Curves (Test Circuit of Figure 11) (Continued)



NOTE:

6. These curves include in the supply current that current fed directly into the load RL from the V+ (See Figure 11). Thus, approximately half the supply current goes directly to the positive side of the load, and the other half, through the HT7660B/HT7660A, to the negative side of the load. Ideally, VOUT ~ 2VIN, IS ~ 2IL, so VIN × IS ~ VOUT × IL.



NOTE: For large values of COSC (>1000pF) the values of C1 and C2 should be increased to 100µF.

FIGURE 11. HT7660B, HT7660A TEST CIRCUIT

Detailed Description

The HT7660B and HT7660A contain all the necessary circuitry to complete a negative voltage converter, with the exception of 2 external capacitors which may be inexpensive 10μ F polarized electrolytic types. The mode of operation of the device may be best understood by considering Figure 12, which shows an idealized negative voltage converter. Capacitor C1 is charged to a voltage, V+, for the half cycle when switches S1 and S 3 are closed. (Note: Switches S2 and S4 are open during this half cycle.) During the second half cycle of operation, switches S2 and S4 are closed, with S1 and S3 open, thereby shifting capacitor C1 negatively by V+ volts. Charge is then transferred from C1 to C2 such that the voltage on C2 is exactly V+, assuming ideal switches and no load on C2. The HT7660B approaches this ideal situation more closely than existing non-mechanical circuits. In the HT7660B and HT7660A, the 4 switches of Figure 12

are MOS power switches; S1 is a P-Channel device and S2,

S3 and S4 are N-Channel devices. The main difficulty with this approach is that in integrating the switches, the

substrates of S3 and S4 must always remain reverse biased with respect to their sources, but not so much as to degrade their "ON" resistances. In addition, at circuit start-up, and

under output short circuit conditions (VOUT = V+), the output voltage must be sensed and the substrate bias adjusted accordingly. Failure to accomplish this would result in high power losses and probable device latchup.

This problem is eliminated in the HT7660B and HT7660A by a logic network which senses the output voltage (VOUT) together with the level translators, and switches the substrates of S_3 and S_4 to the correct level to maintain necessary reverse bias.



The voltage regulator portion of the HT7660B and HT7660A is an integral part of the anti-latchup circuitry, however its inherent voltage drop can degrade operation at low voltages. Therefore, to improve low voltage operation the "LV" pin should be connected to GROUND, disabling the regulator. For supply voltages greater than 3.5V the LV terminal must be left open to insure latchup proof operation, and prevent device damage.




FIGURE 12. IDEALIZED NEGATIVE VOLTAGE CONVERTER

Theoretical Power


Efficiency Considerations

In theory a voltage converter can approach 100% efficiency if certain conditions are met.

- 1. The driver circuitry consumes minimal power.
- 2. The output switches have extremely low ON resistance and virtually no offset.
- 3. The impedances of the pump and reservoir capacitors are negligible at the pump frequency.

The HT7660B and HT7660A approach these conditions for

negative voltage conversion if large values of C1 and C2 are used.



ENERGY IS LOST ONLY IN THE TRANSFER OF CHARGE BETWEEN CAPACITORS IF A CHANGE IN VOLTAGE

OCCURS. The energy lost is defined by:

$$E = \frac{1}{2}C_1 (V_1^2 - V_2^2)$$

where V₁ and V₂ are the voltages on C₁ during the pump and transfer cycles. If the impedances of C₁ and C₂ are relatively high at the pump frequency (refer to Figure 12) compared to the value of R_L, there will be a substantial difference in the voltages

 V_1 and V_2 . Therefore it is not only desirable to make C_2 as large as possible to eliminate output voltage ripple, but also to employ a correspondingly large value for C_1 in order to achieve maximum efficiency of operation.

Do's And Don'ts

- 1. Do not exceed maximum supply voltages.
- 2. Do not connect LV terminal to GROUND for supply voltages greater than 3.5V.
- Do not short circuit the output to V+ supply for supply voltages above 5.5V for extended periods, however, transient conditions including start-up are okay.
- When using polarized capacitors, the + terminal of C1 must be connected to pin 2 of the HT7660B and HT7660A and the + terminal of C2 must be connected to GROUND.
- 5. If the voltage supply driving the HT7660B and HT7660A has a large source impedance $(25\Omega 30\Omega)$, then a 2.2μ F capacitor from pin 8 to ground may be required to limit rate of rise of input voltage to less than $2V/\mu$ s.
- User should insure that the output (pin 5) does not go more positive than GND (pin 3). Device latch up will occur under these conditions. A 1N914 or similar diode placed

in parallel with C_2 will prevent the device from latching up under these conditions. (Anode pin 5, Cathode pin 3).




FIGURE 13A. CONFIGURATION FIGURE 13B. THEVENIN EQUIVALENT FIGURE 13. SIMPLE NEGATIVE

CONVERTER



In a typical application where fOSC = 10kHz and C = C1 =

 $C_2 = 10 \mu F$:

$$RO \cong 2 (23) + \frac{1}{(5 \cdot 10^{3}) (10^{-5})} + 4 (ESRC1) + ESRC2$$

 $RO \cong 46 + 20 + 5 (ESRC)$

Since the ESRs of the capacitors are reflected in the output impedance multiplied by a factor of 5, a high value could potentially

swamp out a low $1/(f_{PUMP} \bullet C_1)$ term, rendering an increase in switching frequency or filter capacitance ineffective. Typical electrolytic capacitors may have ESRs as high as 10Ω .

$$RO \cong 2(23) + \frac{1}{(5 \cdot 10^{3})(10^{-5})} + 4(ESRC1) + ESRC2$$
$$RO \cong 46 + 20 + 5(ESRC)$$

Since the ESRs of the capacitors are reflected in the output impedance multiplied by a factor of 5, a high value could potentially

swamp out a low $1/(f_{PUMP} \bullet C_1)$ term, rendering an increase in switching frequency or filter capacitance ineffective. Typical electrolytic capacitors may have ESRs as high as 10Ω .

Output Ripple

ESR also affects the ripple voltage seen at the output. The total ripple is determined by 2 voltages, A and B, as shown in Figure

14. Segment A is the voltage drop across the ESR of C₂ at the instant it goes from being charged by C₁ (current flow into C₂) to being discharged through the load (current flowing out of C₂). The magnitude of this current change is $2 \cdot I_{OUT}$, hence the total drop is $2 \cdot I_{OUT} \cdot eSR_{C2}V$. Segment B is the voltage

change across C_2 during time t_2 , the half of the cycle when C_2

supplies current to the load. The drop at B is $I_{OUT} \bullet t2/C_2V$. The peak-to-peak ripple voltage is the sum of these voltage drops:

 $\begin{array}{c} 1 \\ VRIPPLE \\ \cong \end{array} \begin{bmatrix} 2 (f_{PUMP}) \\ PUMP \end{bmatrix} (C2) \\ + 2 (ESRC2) \end{bmatrix} OUT$

Again, a low ESR capacitor will reset in a higher performance output.

Paralleling Devices

Any number of HT7660B and HT7660A voltage converters may be paralleled to reduce output resistance. The reservoir

capacitor, C2, serves all devices while each device requires

its own pump capacitor, C1. The resultant output resistance would be approximately:

$$R_{OUT} = \frac{R_{OUT} (of HT7660B/HT7660A)}{n (number of devices)}$$

Cascading Devices

The HT7660B and HT7660A may be cascaded as shown to produced larger negative multiplication of the initial supply voltage. However, due to the finite efficiency of each device, the practical limit is 10 devices for light loads. The output voltage is defined by:

VOUT = -n (VIN),

where n is an integer representing the number of devices cascaded. The resulting output resistance would be approximately the weighted sum of the individual HT7660B

and HT7660A ROUT values.

Changing the HT7660B/HT7660A

Oscillator Frequency

It may be desirable in some applications, due to noise or other considerations, to increase the oscillator frequency. This is achieved by overdriving the oscillator from an external clock, as shown in Figure 17. In order to prevent possible device latchup, a $1k\Omega$ resistor must be used in series with the clock output. In a situation where the designer has generated the external clock frequency using TTL logic, the addition of a $10k\Omega$ pullup resistor to V+ supply is required. Note that the pump frequency with external clocking, as with internal

clocking, will be $^{\prime}/_{2}$ of the clock frequency. Output transitions occur on the positive-going edge of the clock.




FIGURE 17. EXTERNAL CLOCKING

It is also possible to increase the conversion efficiency of the HT7660B and HT7660A at low load levels by lowering the oscillator frequency. This reduces the switching losses, and is shown in Figure 18. However, lowering the oscillator frequency will cause an undesirable increase in the impedance of the pump

(C1) and reservoir (C2) capacitors; this is overcome by

increasing the values of C₁ and C₂ by the same factor that the frequency has been reduced. For example, the addition of a 100pF capacitor between pin 7 (OSC) and V+ will lower the oscillator frequency to 1kHz from its nominal frequency of 10kHz (a multiple of 10), and thereby necessitate a corresponding

increase in the value of C_1 and C_2 (from $10 \mu F$ to $100 \mu F).$



HT7660




FIGURE 18. LOWERING OSCILLATOR FREQUENCY

Positive Voltage Doubling

The HT7660B and HT7660A may be employed to achieve positive voltage doubling using the circuit shown in Figure 19. In this application, the pump inverter switches of the HT7660B and HT7660A are used to charge C1 to a voltage level of V+ - VF (where V+ is the supply voltage and V F is the forward voltage drop of diode D1). On the transfer cycle, the voltage on C1 plus the supply voltage (V+) is applied through diode D2 to capacitor C2. The voltage thus created on C 2 becomes (2V+) - (2VF) or twice the supply voltage minus the combined forward voltage drops of diodes D1 and D2.

The source impedance of the output (VOUT) will depend on the output current, but for V+ = 5V and an output current of 10mA it will be approximately 60Ω .




FIGURE 19. POSITIVE VOLT DOUBLER

Combined Negative Voltage Conversion and Positive Supply Doubling

Figure 20 combines the functions shown in Figures 13 and Figure 19 to provide negative voltage conversion and positive voltage doubling simultaneously. This approach would be, for example, suitable for generating +9V and -5V from an existing

+5V supply. In this instance capacitors C1 and C3 perform the pump and reservoir functions respectively for the

generation of the negative voltage, while capacitors C2 and

C4 are pump and reservoir respectively for the doubled positive voltage. There is a penalty in this configuration which combines both functions, however, in that the source impedances of the generated supplies will be somewhat higher due to the finite impedance of the common charge pump driver at pin 2 of the device.




FIGURE 20. COMBINED NEGATIVE VOLTAGE CONVERTER AND POSITIVE DOUBLER

Voltage Splitting

The bidirectional characteristics can also be used to split a higher supply in half, as shown in Figure 21. The combined load will be evenly shared between the two sides. Because the switches share the load in parallel, the output impedance is much lower than in the standard circuits, and higher currents can be drawn from the device. By using this circuit, and then the circuit of Figure 16, +15V can be converted (via +7.5, and - 7.5) to a nominal -15V, although with rather high series output resistance (~250 Ω).




FIGURE 21. SPLITTING A SUPPLY IN HALF

Regulated Negative Voltage Supply

In some cases, the output impedance of the HT7660B and HT7660A can be a problem, particularly if the load current varies substantially. The circuit of Figure 22 can be used to overcome this by controlling the input voltage, via an ICL7611 low-power CMOS op amp, in such a way as to maintain a nearly constant output voltage. Direct feedback is inadvisable, since the HT7660Bs and HT7660As output does not respond instantaneously to change in input, but only after the switching delay. The circuit shown supplies enough delay to accommodate the HT7660B and HT7660A, while maintaining adequate feedback. An increase in pump and storage capacitors is desirable, and the values shown provides an output impedance of less than 5Ω to a load of 10mA.



HT7660

Other Applications

Further information on the operation and use of the HT7660B and HT7660A may be found in AN051 "Principals and Applications of the HT7660B and HT7660A CMOS Voltage Converter".







FIGURE 22. REGULATING THE OUTPUT VOLTAGE















Dimension, mm

NOTES:

 Dimensions "A", "B" do not include mold flash or protrusions. Maximum mold flash or protrusions 0.25 mm (0.010) per side.

(SOP8)



NOTES:

- 1. Dimensions A and B do not include mold flash or protrusion.
- 2. Maximum mold flash or protrusion 0.15 mm (0.006) per side for A; for B 0.25 mm (0.010) per side.



	1						
	Dimension, mm						
Symbol	MIN	MAX					
А	4.8	5					
В	3.8 4						
С	1.35	1.75					
D	0.33 0.51						
F	0.4 1.27						
G	1.27						
Н	5.	72					
J	0°	8°					
K	0.1 0.25						
М	0.19 0.25						
Р	5.8	6.2					
R	0.25 0.5						