

ABSO5 THRU ABS 10 SINGLE PHASE 1.0 AMP SURF ACE MOUNT BRIDGE RECTIFIERS




FEATURES

- * Ideal for printed circuit board
- * Reliable low cost construction utilizing molded plastic technique
- * High surge current capability
- * Polarity: Symbol molded on body
- * Mounting position: Any
- * Weight: 0.12 grams

VOLTAGE RANGE 50 to 1000 Volts CURRENT

1.0 Ampere



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

TYPE NUMBER	ABS05	ABS1	ABS2	ABS4	ABS6	ABS8	ABS10	UNITS
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V
Maximum RMS Voltage	35	70	140	280	420	560	700	V
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V
Maximum Average Forward Rectified Current								
at Ta=40°C(Note 1)	1.0							Α
Peak Forward Surge Current, 8.3 ms single half sine-wave								
superimposed on rated load (JEDEC method)	3 0						Α	
Maximum Forward Voltage Drop per Bridge Element at 0.4A D.C.	1.0						V	
Maximum DC Reverse Current Ta=25°C	5.0							μΑ
at Rated DC Blocking Voltage Ta=125°C	500							μΑ
Typical Thermal Resistance R JA (Note 2)	75					°C/W		
Operating Temperature Range, TJ	-55—+150						°C	
Storage Temperature Range, Тятс	-55—+150							°C

NOTES: 1. Mounted on P.C. Board.

2. Thermal Resistance Junction to Ambient.

RATING AND CHARACTERISTIC CURVES (ABS05 THRU ABS10)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3-TYPICAL FORWARD




FIG.4-TYPICAL REVERSE

