




SINGLE PHASE 2.0 AMP BRIDGE RECTIFIERS

FEATURES

- * Ideal for printed circuit board
- * Low forward voltage
- * Low leakage current
- * Polarity: marked on body
- * Mounting position: Any
- * Weight: 4.8 grams

VOLTAGE RANGE 600 to 1000 Volts CURRENT 2.0 Ampere



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

	Symbols	GBP206	GBP208	GBP210	Units
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	600	800	1000	Volts
Maximum RMS Voltage	V _{RMS}	420	560	700	Volts
Maximum DC Blocking Voltage	V _{DC}	600	800	1000	Volts
Maximum Average Forward Rectified Current	T .		2.0	•	A
.375"(9.5mm) Lead Length at T _A =50	I _(AV)	2.0			Amp
Peak Forward Surge Current,					
8.3ms single half-sine-wave	I_{FSM}	I _{FSM} 50			Amp
superimposed on rated load (JEDEC method)					
Maximum Forward Voltage	$V_{\rm F}$	1.1			Volts
at 2.0A DC and 25	V _F				
Maximum Reverse Current at T _A =25	T	5.0			uAmp
at Rated DC Blocking Voltage T _A =100	1 _R	I _R 500			
Typical Junction Capacitance (Note 1)	C _J	25			pF
Typical Thermal Resistance (Note 2)	$R_{\theta JA}$	30			/W
Typical Thermal Resistance (Note 2)	$R_{\theta,JL}$	16			/W
Operating and Storage Temperature Range	T _J , Tstg	-55 to +150			

NOTES:

- 1- Measured at 1 $\ensuremath{\text{MH}_{\text{Z}}}$ and applied reverse voltage of 4.0 VDC.
- 2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375"(9.5mm) lead length P.C.B. Mounted.

RATING AND CHARACTERISTIC CURVES (GBP206 THRU GBP210)

FIG.1-TYPICAL FORWARD CURRENT **DERATING CURVE**




FIG.2-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3-TYPICAL FORWARD






FIG.4-TYPICAL REVERSE

