


GBP306 THRU GBP310

SINGLE PHASE 3.0 AMP BRIDGE RECTIFIERS

FEATURES

- * Ideal for printed circuit board
- * Low forward voltage
- * Low leakage current
- * Polarity: marked on body
- * Mounting position: Any
- * Weight: 4.8 grams



MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature uniess otherwies specified. Single phase half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

| | Symbols | GBP306 | GBP308 | GBP310 | Units |
|--|---------------------|--------|-------------|--------|-------|
| Maximum Recurrent Peak Reverse Voltage | V _{RRM} | 600 | 800 | 1000 | Volts |
| Maximum RMS Voltage | V _{RMS} | 420 | 560 | 700 | Volts |
| Maximum DC Blocking Voltage | V _{DC} | 600 | 800 | 1000 | Volts |
| Maximum Average Forward Rectified Current | T | | 3.0 | | Amp |
| .375"(9.5mm) Lead Length at T _A =50 | I _(AV) | | | | |
| Peak Forward Surge Current, | | | | | |
| 8.3ms single half-sine-wave | I _{FSM} 70 | | | Amp | |
| superimposed on rated load (JEDEC method) | | | | | |
| Maximum Forward Voltage | V _F 1.1 | | | Volts | |
| at 3.0A DC and 25 | v _F 1.1 | | | | |
| Maximum Reverse Current at T _A =25 | T | 10.0 | | | |
| at Rated DC Blocking Voltage T _A =100 | I _R 500 | | | uAmp | |
| Typical Junction Capacitance (Note 1) | CJ | 25 | | | pF |
| Typical Thermal Resistance (Note 2) | R _{0JA} | 30 | | | /W |
| Typical Thermal Resistance (Note 2) | $R_{\theta JL}$ | 16 | | | /W |
| Operating and Storage Temperature Range | T_J , Tstg | | -55 to +150 | | |

NOTES:

1- Measured at 1 MH_Z and applied reverse voltage of 4.0 VDC.

2- Thermal Resistance Junction to Ambient and form junction to lead at 0.375"(9.5mm) lead length P.C.B. Mounted.

RATING AND CHARACTERISTIC CURVES (GBP306 THRU GBP310)





FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS PER BRIDGE ELEMENT







FIG.4- TYPICAL REVERSE CHARACTERISTICS PER BRIDGE ELEMENT



www.gk-goodwork.com.