



KBJ10005 THRU KBJ1010

SINGLE PHASE 10.0 AMP BRIDGE RECTIFIERS



FEATURES


- * Ideal for printed circuit board
- * Low forward voltage
- * Low leakage current
- * Mounting position: Any

VOLTAGE RANGE

50 to 1000 Volts

CURRENT

4.0 Amperes



Dimensions in inches and (millimeters)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Rating 25°C ambient temperature unless otherwise specified.
Single phase half wave, 60Hz, resistive or inductive load.
For capacitive load, derate current by 20%.

TYPE NUMBER	KBJ10005	KBJ1001	KBJ1002	KBJ1004	KBJ1006	KBJ1008	KBJ1010	UNITS	
Maximum Recurrent Peak Reverse Voltage	50	100	200	400	600	800	1000	V	
Maximum RMS Voltage	35	70	140	280	420	560	700	V	
Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V	
Maximum Average Forward (with heatsink Note 2)								10.0	A
Rectified Current at T _c =110°C (Without heatsink)								3.0	A
Peak Forward Surge Current, 8.3 ms single half sine-wave superimposed on rated load (JEDEC method)								200	A
Maximum Forward Voltage Drop per Bridge Element at 5.0A D.C.								1.05	V
Maximum DC Reverse Current at Rated DC Blocking Voltage								5.0	µA
Typical Thermal Resistance R _{jc} (Note 1)								2.3	°C/W
Typical Thermal Resistance R _{jl} (Note 2)								6.0	°C/W
Operating Temperature Range, T _J								-55 — +150	°C
Storage Temperature Range, T _{STG}								-55 — +150	°C

NOTES:

1. Thermal Resistance from Junction to Case with device mounted on 100mm x 100mm x 1.6mm Cu Plate Heatsink.
2. Thermal Resistance from Junction to Lead without Heatsink.

RATING AND CHARACTERISTIC CURVES (KBJ10005 THRU KBJ1010)

FIG.1-TYPICAL FORWARD CURRENT DERATING CURVE




FIG.2-MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3-TYPICAL FORWARD CHARACTERISTICS




FIG.4-TYPICAL REVERSE CHARACTERISTICS

