



Rated electric load: DC12V 50mA  
 额定电负荷: DC12V 50mA  
 Insulation resistance:  $\geq 100M\Omega$   
 绝缘电阻:  $\geq 100M\Omega$   
 Withstand voltage strength: AC250V 50Hz / lmin  
 耐压强度: AC250V 50Hz / lmin  
 Electrical life: 10000 cycles min  
 电气寿命: 10000 cycles min

Ambient temperature:  $-25^{\circ}C \sim +70^{\circ}C$   
 环境温度:  $-25^{\circ}C \sim +70^{\circ}C$   
 Relative humidity:  $(40^{\circ}C) \leq 95\%$   
 相对湿度:  $(40^{\circ}C) \leq 95\%$   
 Contact resistance:  $\leq 100m\Omega$   
 接触电阻:  $\leq 100m\Omega$   
 Action force:  $200gf \pm 100gf$   
 力度:  $200gf \pm 100gf$

E	Terminal	6	Brass(0.30t)	ag Plated
D	Contact spring	1	Phosphor bronze	ag Plated
C	Base	1	Pa46	Black
B	Cover	1	SUS	Natural
A	Keystake	1	Pa46	Black
Serial number	NAME	QUANTITY	Texture of material	Plating/colour

A4				
A3				
A2				
A1				
REV	DATE	REVISION	DESCRIPTION	ISSUE



COMMON TOLERANCE

X.XX	$\pm 0.10$
X.X	$\pm 0.15$
X	$\pm 0.25$
ANGULAR	—

UNIT	MM	PROJECTED		PRODUCT NAME:
DRAWN BY	FUYUAN	CHECKED BY	COCO	MODEL NO: TP-33104
DATE	2019	APPROVAL B	ALEN	Https: www.rocpcu.tw
<b>ROCPCU TECHNOLOGY CO.,LTD</b>				
Copies are issued in strict confidence and shall not be reproduced or copied, or used as the basic of manufacture or sale of apparatus without permission				