






REV.	DESCRIPTION	ECN No.	DATE
A0	△新版发行		2017-02-24

B12	GND
B9	VBUS
B5	CC2
A5	CC1
A9	VBUS
A12	GND
PIN	SIGNAL NAME



- NOTES:
- 1.MATERIAL:  
MOLDING: LCP UL94 V-0  
CONTACT: COPPER ALLOY.  
GOLD PLATED Min ON CONTACT AREA, 100u" Min TIN (LEAD FREE) ON SOLDER AREA, SHELL: SUS201-H,T=0.30±0.03mm 50u" NICKEL PLATING OVER ALL.
  - 2.MECHANICAL:  
INSERTION: 5~20N.  
EXTRACTION: 8~20N AFTER TEST.  
DURABILITY: 5000 CYCLES
  - 3.ELECTRICAL:  
CURRENT: 3A FOR VBUS,  
1.25A FOR GND PIN,  
0.25A FOR OTHER  
VOLTAGE: 20 V MAX  
WITHSTANDING VOLTAGE: 100V AC R.M.S,  
CONTACT RESISTANCE: 40mΩ MAX,  
INSULATION RESISTANCE: 100MΩ MIN.
  - 4.ENVIRONMENTAL  
TEMPERATURE RANGE -25°C ~ +85°C
  5. 尺寸标注事项:  
图示有标注的“者为首样全检, 重点管控尺寸.”
  6. 产品符合RoHS标准

东莞市美韩电子科技有限公司  
Dongguan Usakro Electronic Technology Co., Ltd.

X: ±0.35	X': ±1.5'	INTENDED USE:	TITLE:
.XX: ±0.25	.XX': ±1.0'	CONNECTOR	USB TYPE C 6PIN沉板1.6简易版
MAT'L: ±0.20	.XXX': ±0.5'	Appd.:	PART NO.:
SEE NOTES	CHKD.:	DR.: Len.Song	SCALE: 1:1
FINISH:			UNIT: mm
			REV.: A0
			PAGE: 1/1
			DWG. NO.: TYPE-C-6M-007
			SEE IABLE