

DESCRIPTION


The SM05C is designed for applications requiring transient overvoltage protection capability. They are intended for use in voltage and ESD sensitive equipment such as computers, printers, business machines, communication systems, medical equipment and other applications. These devices are ideal for situations where board space is at a premium.

This series has been specifically designed to protect sensitive components which are connected to power, data and transmission lines from overvoltage caused by ESD(electrostatic discharge), CDE (Cable Discharge Events), and EFT (electrical fast transients).

ORDERING INFORMATION

- ♦Device:SM05C
- ♦Package: SOT-23
- ♦Material: Halogen free
- ♦Packing: Tape & Reel
- ♦Quantity per reel: 3,000pcs

PIN CONFIGURATION



Bidirectional TVS Diode Array

SM05C

FEATURES

- ♦IEC61000-4-2 (ESD) ±15kV (air), ±8kV (contact)
- ♦IEC61000-4-4 (EFT) 40A (5/50ηs)
- ♦Protects two bidirectional lines
- ♦Low clamping voltage
- ♦Low leakage current

MACHANICAL DATA

- ♦SOT-23 package
- ♦ Flammability Rating: UL 94V-0
- ♦Packaging: Tape and Reel
- \diamond High temperature soldering guaranted:260 $^{\circ}$ C /10s
- ♦Reel size: 7 inch

♦MSL 1

APPLICATIONS

- ♦ Cell Phone Handsets and Accessories
- Microprocessor based equipment
- ♦ Personal Digital Assistants (PDA's)
- ♦Notebooks, Desktops, and Servers
- \diamond Portable Instrumentation
- ♦Networking and Telecom
- ♦ Serial and Parallel Ports.
- ♦Peripherals

PACKAGE OUTLINE





SM05C Bidirectional TVS Diode Array


BSOLUTE MAXIMUM RATING						
Symbol	Parameter	Value	Units			
V _{ESD}	ESD per IEC 61000-4-2 (Air) ESD per IEC 61000-4-2 (Contact)	±15 ±8	kV			
P _{PP}	Peak Pulse Power (8/20µs)	350	W			
T _{OPT}	Operating Temperature	-55/+150	°C			
T _{STG}	Storage Temperature	-55/+150	°C			
TL	Lead Soldering Temperature	260 (10 sec.)	°C			


ELECTRICAL CHARACTERISTICS (Tamb=25°C)									
PART NUMBER	DEVICE MARKING	V _{RWM} (V) (max.)	V _B (V) (min.)	Ι _τ (mA)	V _C @1A (V) (max.)	۷ (/ (max.)	-	Ι _R (μΑ) (max.)	C _J (pF) (max.)
SM05C	C05	5.0	6.0	1	9.8	18.0	17	10	200




SM05C Bidirectional TVS Diode Array

ELECTRICAL CHARACTERISTICS CURVE







Pulse Waveform



SOT-23 PACKAGE OUTLINE DIMENSIONS





	MILLIMETERS			INCHES		
DIM	MIN	NOM	MAX	MIN	NOM	MAX
Α	0.89	1.00	1.11	0.035	0.040	0.044
A1	0.01	0.06	0.10	0.001	0.002	0.004
b	0.37	0.44	0.50	0.015	0.018	0.020
С	0.09	0.13	0.18	0.003	0.005	0.007
D	2.80	2.90	3.04	0.110	0.114	0.120
E	1.20	1.30	1.40	0.047	0.051	0.055
е	1.78	1.90	2.04	0.070	0.075	0.081
L,	0.35	0.54	0.69	0.014	0.021	0.029
HE	2.10	2.40	2.64	0.083	0.094	0.104

