

# SS22F-AT THRU SS220F-AT

## SURFACE MOUNT SCHOTTKY BARRIER RECTIFIERS

Forward Current-2.0A

Reverse Voltage-20V to 200V

### FEATURES


- ◆ For surface mount applications
- ◆ High forward surge current capability
- ◆ Low power loss,high efficiency
- ◆ Metal silicon junction,majority carriers conduction

### MECHANICAL DATA

- ◆ Case: SMAF molded plastic body
- ◆ Terminals: Solderable per MIL-STD-750 , Method 2026
- ◆ Weight: Approximated 0.027 grams

### PINNING

PIN	DESCRIPTION
1	Cathode
2	Anode



### MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS

Ratings at 25°C ambient temperature unless otherwise specified.

Single phase half-wave 60 Hz, resistive or inductive load, for capacitive load current derating by 20 %.

PARAMETER	SYMBOL	SS22F-AT	SS24F-AT	SS26F-AT	SS28F-AT	SS210F-AT	SS212F-AT	SS215F-AT	SS220F-AT	UNIT
Maximum Repetitive Peak Reverse Voltage	$V_{RRM}$	20	40	60	80	100	120	150	200	V
Maximum RMS Voltage	$V_{RMS}$	14	28	42	56	70	84	105	140	V
Maximum DC Blocking Voltage	$V_{DC}$	20	40	60	80	100	120	150	200	V
Maximum Average Forward Rectified Current at $T_C=100^\circ\text{C}$	$I_{F(AV)}$	2.0								A
Peak Forward Surge Current (Note1)	$I_{FSM}$	50				40				A
Maximum Forward Voltage at 2.0 A	$V_F$	0.55	0.70		0.85		0.95		V	
Maximum DC Reverse Current at Rated DC Blocking Voltage at $T_A=25^\circ\text{C}$ $T_A=100^\circ\text{C}$	$I_R$	0.5 5			0.3 3				mA	
Typical Junction Capacitance(Note2)	$C_J$	160	80							pF
Typical Thermal Resistance (Note3)	$R_{\theta JA}$	80								°C/W
Operating and Storage Temperature Range	$T_J, T_{STG}$	-55 to +150								°C

Notes: 1. Measured at 8.3 ms single half sine wave superimposed on rated load (JEDEC Method).

2. Measured at 1MHz and applied reverse voltage of 4 V D.C.

3. P.C.B. mounted with 2.0" X 2.0" (5 X 5 cm) copper pad areas.

# SS22F-AT THRU SS220F-AT

## RATINGS AND CHARACTERISTIC CURVES

Fig.1 Forward Current Derating Curve




Fig.2 Typical Reverse Characteristics




Fig.3 Typical Forward Characteristics




Fig.4 Typical Junction Capacitance




Fig.5 Maximum Non-Repetitive Peak Forward Surge Current






Fig.6 Typical Transient Thermal Impedance



# SS22F-AT THRU SS220F-AT

## PACKAGE OUTLINE

### SMAF



### Marking

Type number	Marking code
SS22F-AT	SS22
SS24F-AT	SS24
SS26F-AT	SS26
SS28F-AT	SS28
SS210F-AT	SS210
SS212F-AT	SS212
SS215F-AT	SS215
SS220F-AT	SS220