


Technical Data

Material:
 Contact Material: Phosphor Bronze
 Contact plating: Au or Sn Over 50μ" Ni
 Insulator Material: Black Polyester UL94V-0
 Standard: PA6T+30%G.F

Electrical:
 Current rating: 2.0Amps/contact max.
 Contact resistance: ≤20mΩ/contact
 Insulation resistance: ≥1000MΩ at V=100V
 Withstanding Voltage: 500V AC/minute

Mechanical:
 Mechanical life cycle: min.200
 Operating temperature: -40°C to +105°C
 Soldering temperature: +255°C



PM	200	V	-	11	-	XXX	-	43		XX		X		N		U		028
品名 PM=排母	间距 2.00mm	产品折弯类型 V=直插 R=弯插 VS=立式贴片 RS=卧式贴片		产品类型 11=单塑单排		PIN位总数 02-40P		塑高 43=4.30mm		表面处理 SN Tin100u" GF Gold Flash G1 Gold 1u" G2 Gold 2u" G3 Gold 3u" G4 Gold 5u" G5 Gold 8u" G6 Gold 10u" G7 Gold 15u" G8 Gold 30u"		塑胶材质 A=PBT C=PA6T E=PA9T		塑胶特性 N=常规 W=带柱		塑胶类型 U=L型 Y=Y型		端子PC/脚宽

				TOLERANCE UNLESS OTHERWISE		DRAWN	CK tan	XFCN兴飞连接器有限公司 CONNECTORS XFCN CONNECTORS CO., LTD.				SHEET	1/1
				X.	±0.30	X°	±5°					CHKD	
				.X	±0.20	.X°	±2°	APPD		PRODUCT NAME	排母2.00mm 单塑单排 塑高4.3 U端	UNITS	mm
				.XX	±0.08	.XX°	±1°			PART. NO.	PM200V-11-XXX-43XXXNU028	SCALE	1:1
AO	MODIFICATION		DRAW	DATE	.XXX	±0.03	.XXX°	±0.5°	VIEW			DWG. NO.	009