






-  Meets IEEE 802.3 & ANSI X3.263 Standards.
-  RoHS Compliant.
-  10/100 Base-T, Through-Hole Type.
-  Operating temperature range: 0°C to +70°C



### Electrical Specifications @25°C

Part Number	OCL(uH Min) @100KHz,0.2V With 8mA DC Bias	Turns Ratio (±5%)	Insertion Loss (dB Max)	Return Loss (dB Min)			Cross talk (dB Min)		CMRR (dB Min)	HI-POT (Vrms)
				0.5-100MHz	0.5-30MHz	30.1-60MHz	60.1-80MHz	0.5-40MHz		
H4001DG	350	1CT:1CT	-1.1	-18	-18+20*log(f/30)	-12	-35	-33+20*log(f/50)	-30	1500

## MECHANICAL



Unless otherwise specified all tolerances are:±0.25 in mm

## SCHEMATICS

